



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks Accessories + End Sections

EK2.5
SNK705910R0000
472597059100
EK2.5 End Section - Dark Grey
Unique dark grey color that fits all terminal blocks colours and ease the id entification of circuits within your terminal block assemblies, - Compatible vith ZK2.5, ZK2.5-PE, ZK4, ZK4-PE, ZK6 and ZK6-PE PI-Spring screwless erminal blocks.
Dark Grey
20 piece
39269097
1SNK160027C0201
1SNK160027C0201
2 mm
52.2 mm
33.6 mm
1.8 g
2 mm
End Sections
acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Polyamide
G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715

Suitable For:	ZK2.5 ZK2.5-PE ZK4 ZK4-PE ZK6 ZK6-PE
Technical UL/CSA	
Flammability According to UL94:	V0
Environmental	
Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
RoHS Status:	Following EU Directive 2011/65/EU
Certificates and Declarations (D	ocument Number)
Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230535F0201
Classifications	
Object Classification Code:	X
Container Information	
	20 piece
Package Level 1 Units:	20 piece
Package Level 1 Units: Package Level 1 Width:	130 mm
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length:	130 mm 280 mm
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length: Package Level 1 Height:	130 mm 280 mm 0 mm
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length:	130 mm 280 mm
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length: Package Level 1 Height: Package Level 1 Gross Weight:	130 mm 280 mm 0 mm 0.055 kg
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length: Package Level 1 Height: Package Level 1 Gross Weight: Package Level 1 EAN:	130 mm 280 mm 0 mm 0.055 kg 3472597059100
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length: Package Level 1 Height: Package Level 1 Gross Weight: Package Level 1 EAN: Package Level 2 Units:	130 mm 280 mm 0 mm 0.055 kg 3472597059100 2900 piece
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length: Package Level 1 Height: Package Level 1 Gross Weight: Package Level 1 EAN: Package Level 2 Units: Package Level 2 Width:	130 mm 280 mm 0 mm 0.055 kg 3472597059100 2900 piece 300 mm
Package Level 1 Units: Package Level 1 Width: Package Level 1 Depth / Length: Package Level 1 Height: Package Level 1 Gross Weight: Package Level 1 EAN: Package Level 2 Units: Package Level 2 Width: Package Level 2 Depth / Length:	130 mm 280 mm 0 mm 0.055 kg 3472597059100 2900 piece 300 mm 300 mm

