

Barton Adaptable Boxes are manufactured from steel and are available with plain sides or knock-outs. The standard finishes are Black Enamel and Hot Dipped Galvanised. (Pre-galvanized lids).


Where boxes are supplied with knock-outs the number and size are as follows:

| Width of side | Number of K.O.s in each side | Size of K.O. |
|---------------|------------------------------|--------------|
| 3" | 2 | 20mm |
| 4" | 3 | 20mm |
| 6" | 4 | 20mm |
| 9" | 6 | 20mm |
| 12" | 6 | 20mm |

Flanged lids are fitted as standard to all boxes and are secured by M5 x 8mm mushroom head screws.

The complete range is manufactured in accordance with BS 4568 Part 2.


A range of Pre-Galvanized Adaptable Boxes are also available on request.



Adaptable Boxes, Plain

R261

| mm | Size | Pack Qty |
|------------------|-------------|----------|
| | Inches | |
| 75 x 75 x 37.5 | 3 x 3 x 1½ | 10 |
| 75 x 75 x 50 | 3 x 3 x 2 | 10 |
| 75 x 75 x 75 | 3 x 3 x 3 | 6 |
| 100 x 75 x 37.5 | 4 x 3 x 1½ | 10 |
| 100 x 75 x 50 | 4 x 3 x 2 | 10 |
| 100 x 100 x 37.5 | 4 x 4 x 1½ | 10 |
| 100 x 100 x 50 | 4 x 4 x 2 | 10 |
| 100 x 100 x 75 | 4 x 4 x 3 | 6 |
| 150 x 75 x 37.5 | 6 x 3 x 1½ | 6 |
| 150 x 75 x 50 | 6 x 3 x 2 | 6 |
| 150 x 75 x 75 | 6 x 3 x 3 | 6 |
| 150 x 100 x 37.5 | 6 x 4 x 1½ | 6 |
| 150 x 100 x 50 | 6 x 4 x 2 | 6 |
| 150 x 100 x 75 | 6 x 4 x 3 | 6 |
| 150 x 50 x 37.5 | 6 x 6 x 1½ | 6 |
| 150 x 50 x 50 | 6 x 6 x 2 | 6 |
| 150 x 50 x 75 | 6 x 6 x 3 | 4 |
| 150 x 50 x 100 | 6 x 6 x 4 | 2 |
| 225 x 75 x 37.5 | 9 x 3 x 1½ | 6 |
| 225 x 75 x 50 | 9 x 3 x 2 | 6 |
| 225 x 75 x 75 | 9 x 3 x 3 | 6 |
| 225 x 150 x 37.5 | 9 x 6 x 1½ | 4 |
| 225 x 150 x 50 | 9 x 6 x 2 | 4 |
| 225 x 150 x 75 | 9 x 6 x 3 | 4 |
| 225 x 150 x 100 | 9 x 6 x 4 | 2 |
| 225 x 225 x 50 | 9 x 9 x 2 | 2 |
| 225 x 225 x 75 | 9 x 9 x 3 | 2 |
| 225 x 225 x 100 | 9 x 9 x 4 | 1 |
| 300 x 150 x 50 | 12 x 6 x 2 | 2 |
| 300 x 150 x 75 | 12 x 6 x 3 | 2 |
| 300 x 150 x 100 | 12 x 6 x 4 | 2 |
| 300 x 225 x 50 | 12 x 9 x 2 | 2 |
| 300 x 225 x 75 | 12 x 9 x 3 | 1 |
| 300 x 225 x 100 | 12 x 9 x 4 | 1 |
| 300 x 300 x 50 | 12 x 12 x 2 | 2 |
| 300 x 300 x 75 | 12 x 12 x 3 | 1 |
| 300 x 300 x 100 | 12 x 12 x 4 | 1 |



Adaptable Boxes, with knock-outs

R262