

DATA - SHEET 1053**No. 1053/RS****Page. 1 of 1****Date. 30 / 11 / 2005****TOOL STEEL / BITS**Description:-

Two grades :- M2 contains 5% Molybdenum
M42 contains 8% Molybdenum

Square Bits have ends ground with 15° angle

Manufacturing Standards:
Metric Tool Bits DIN 4964
Inch Tool Bits ISO 5421

RS STOCK NUMBER	Linear Code	DESCRIPTION	Section	Length
5227698	29-003-384	Tool Steel M2	ROUND 1/4" dia.	4"
5227727	29-003-385	Tool Steel M2	5/16" dia.	4"
5227705	29-003-389	Tool Steel M2	3/8" dia.	4"
5227711	29-003-387	Tool Steel M2	1/2" dia.	4"
			SQUARE	
5227733	29-002-662	Tool Steel M2	1/4" x 1/4"	2/12"
5227755	29-002-664	Tool Steel M2	1/4" x 1/4"	4"
5227761	29-002-666	Tool Steel M2	5/16" x 5/16"	3"
5227777	29-002-667	Tool Steel M2	5/16" x 5/16"	4"
5227783	29-002-668	Tool Steel M2	3/8" x 3/8"	3"
5227799	29-002-669	Tool Steel M2	3/8" x 3/8"	4"
5227812	29-002-676	Tool Steel M2	3/8" x 3/8"	6"
5227828	29-002-670	Tool Steel M2	1/2" x 1/2"	4"
5227834	29-002-671	Tool Steel M2	1/2" x 1/2"	6"
			ROUND	
5227840	29-042-829	Tool Steel M42	3/16" dia.	4"
5227856	29-042-834	Tool Steel M42	1/4" dia.	4"
5227862	29-042-391	Tool Steel M42	5/16" dia.	3"
5227878	29-042-393	Tool Steel M42	3/8" dia.	4"
5227884	29-042-387	Tool Steel M42	1/2" dia.	4"
			SQUARE	
5227890	29-042-716	Tool Steel M42	3/16" x 3/16"	3"
5227907	29-042-723	Tool Steel M42	1/4" x 1/4"	3"
5227913	29-042-724	Tool Steel M42	1/4" x 1/4"	4"
5227929	29-042-726	Tool Steel M42	5/16" x 5/16"	3"
5227935	29-042-727	Tool Steel M42	5/16" x 5/16"	4"
5227941	29-042-728	Tool Steel M42	3/8" x 3/8"	3"
5227957	29-042-729	Tool Steel M42	3/8" x 3/8"	4"
5227979	29-042-735	Tool Steel M42	3/8" x 3/8"	6"
5227985	29-042-738	Tool Steel M42	1/2" x 1/2"	3"
5227991	29-042-730	Tool Steel M42	1/2" x 1/2"	4"
5228001	29-042-731	Tool Steel M42	1/2" x 1/2"	6"