



CONTACT • REQUEST A QUOTE

PRODUCTS

RESOURCES

COMPANY

PART NUMBER SEARCH

« Clamping Knobs

## Three Arm Clamping Knobs

### Series #3040

Clamping knobs are available in different materials, thermoplastic, and phenolic for a multiple of applications.

A variety of shapes and diameters with plain, tapped bosses or with studs are available with standard threads to fit the application.

Perfect for the industrial machinery, medical, general equipment and other industrial applications.

Knobs can be decorated or customized to your specific need.

Davies Molding is pleased to introduce our series of soft touch knobs and handles. Our soft touch parts are molded with a soft thermoplastic overmolded "rubber" top with a tough thermoplastic body underneath. The soft feel of the knob provides a comfortable touch with a sure grip.


Colors available upon request.

Please note: Not all variations available are listed below. Please [contact Customer Service](#) to inquire about all available options.



REQUEST CAD DRAWING

REQUEST A QUOTE



Item #	Diameter A	Height B	Hub C	Material Type	Mounting Diameter	Mounting Type	Thread Length/Depth	Color
3040-A	2	1.25	0.75	Thermoset	5/16-18	Female Insert	0.50	BLACK
3040-C	2	1.25	0.75	Thermoset	3/8-16	Projecting Stud	0.75	BLACK
3040-E	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	0.56	BLACK
3040-F	2	0.75	0.75	Thermoset	1/4-20	Female Insert	0.375	BLACK
3040-G	2	1.00	0.75	Thermoset	3/8-24	Female Insert	0.625	BLACK
3040-J	2	0.75	0.75	Thermoset	5/16-18	Projecting Stud	0.75	BLACK
3040-M	2	1.00	0.75	Thermoset	5/16-18	Female Insert	0.50	BLACK
3040-R	2	1.00	0.75	Thermoset	0.33	Square Thru-Hole		BLACK
3040AF	2	1.00	0.75	Thermoset	1/4-20	Female Insert	0.375	BLACK
3040AH	2	1.00	0.75	Thermoset	3/8-16	Female Insert	0.50	BLACK
3040AL	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	1.00	BLACK
3040AM	2	0.75	0.75	Thermoset	1/4-20	Projecting Stud	1.50	BLACK
3040AP	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	1.50	BLACK
3040BF	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	0.75	BLACK
3040BH	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	1.00	BLACK

3040BL	2	1.00	0.75	Thermoset	10-24	Female Insert	0.375	BLACK
3040BM	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	1.00	BLACK
3040BW	2	1.00	0.75	Thermoset	3/8-16	Female Insert	0.625	BLACK
3040CG	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	0.75	BLACK
3040CH	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	1.125	BLACK
3040CK	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	2	BLACK
3040CQ	2	1.00	0.75	Thermoset	5/16-18	Thru-Hole		BLACK
3040CU	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	1.25	BLACK
3040CW	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	1.75	BLACK
3040DC	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	0.75	BLACK
3040DM	2	1.25	0.75	Thermoset	3/8-16	Female Insert	0.75	BLACK
3040DN	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	2	BLACK
3040DT	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	1.25	BLACK
3040DX	2	1.00	0.75	Thermoset	5/16-24	Female Insert	0.50	BLACK
3040ED	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	0.375	BLACK
3040EH	2	1.25	0.75	Thermoset	1/4-28	Thru-Hole		BLACK
3040EJ	2	1.25	0.75	Thermoset	3/8-16	Female Insert	0.50	BLACK
3040EL	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	1.75	BLACK
3040EX	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	1.50	BLACK
3040FA	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	0.625	BLACK
3040FD	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	0.50	BLACK
3040FS	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	2.25	BLACK
3040GG	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	0.625	BLACK
3040GJ	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	0.50	BLACK
3040GS	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	2.25	BLACK
3040GU	2	1.00	0.75	Thermoset	5/16-18	Projecting Stud	2	BLACK
3040GX	2	1.00	0.75	Thermoset	1/4-20	Projecting Stud	1.25	BLACK
3040HC	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	3.00	BLACK
3040HG	2	1.00	0.75	Thermoset	3/8-24	Projecting Stud	1.25	BLACK
3040HK	2	1.00	0.75	Thermoset	3/8-16	Projecting Stud	2.50	BLACK
3040JE	2	1.00	0.75	Thermoset	3/8-16	Female Insert	0.50	BLACK
3040JM	2	1.00	0.75	Thermoset	3/8-16	Thru-Hole		BLACK
3040JT	2	1.00	0.75	Thermoset	3/8-16	Female Insert	0.625	RED
3040JU	2	0.75	0.75	Thermoset	3/8-16	Projecting Stud	1.50	BLACK

## PRODUCTS

Knobs  
Handles  
Leveling Feet  
Latches  
Hinges  
Indexing Plungers  
Electronic Enclosures  
Two-Shot / Soft Touch  
Frac Balls  
Custom Molding

## RESOURCES

Engineering Specifications  
Distributor Listing  
Sales Representative Listing

## COMPANY

About Us  
Capabilities  
Certifications  
Contact Us  
Blog  
Careers

## QUESTIONS ?

questions / comments

Copyright © 2016 Davies Molding, LLC. All Rights Reserved.

350 Kehoe Blvd. | Carol Stream, IL 60188-1818 | Phone: (800) 554-9208 | Fax: (630) 510-9944