



Actual product may vary from the image shown

Professional Wired Desktop for Entry Level Users

The compact and high-quality JD-0800EU-2 desktop set from CHERRY, features an excellent price/performance ratio, modern, flat design with gentle, quiet and durable wear-resistant keys.

Facts & Features

- Whisper quiet keystroke keys with wear-resistant laser key legends
- 4 hot-keys (calculator, e-mail, browser, sleep mode)
- Up to 10 million keystrokes
- Symmetrical design: 3-Button mouse, suitable for both left-handed and right-handed operation
- Optical Sensor technology: 1200 dpi
- Rapid installation: Simple plug and play via 1 USB connection for keyboard and 1 USB connection for mouse

Technical Data

Housing and Key Color:
Black

Weight (product):

Approx. 530 g/1.16 lbs (keyboard),
Approx. 90 g/ .19 lbs (mouse)

Total Weight (with packaging):

Approx. 896 g/ 1.97 lbs

Technical Data Cont.

Cable Length:

Approx. 1.80 m/ 5.9' (keyboard)
Approx. 1.80 m/ 5.9' (mouse)

Storage Temperature:

-20°C to 65°C / -4°F to 149°F

Operating Temperature:

0° C to 50° C / 32° F to 122° F

Current Consumption:

Max. 50 mA (keyboard), max. 50 mA (mouse)

Interface:

USB

Product Approvals:

C-Tick



UL



CE



FCC



TÜV/GS



System Requirements:

2 USB connections for keyboard and mouse

Delivery Volume:

- Operating instructions in hard copy
- 1 corded keyboard
- 1 corded mouse

Dimensions (product):

458 x 170 x 20 mm / 18.03" x 6.69" x .78"
(keyboard), 109 x 62 x 37mm / 4.2" x 2.4" x
1.4" (mouse)

Packaging Dimensions:

Approx. 546 x 198 x 45 mm / 21.19" x
7.79" x 1.77"



Technical Data Cont.

Reliability:

- MTBF > 45,000 hours

Mouse:

- Scanning: Optical
- Resolution: 1200 dpi
- Number of keys: 3
- Mouse wheel design:
Scroll wheel with key function
- Design: Symmetrical
- Connection: USB
- Housing color: Black
- Key color: Black

Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Number of keys: 104
- Number of additional keys: 4

Packaging Unit:

Number of products in the master package: 6

Number of master packages per pallet: 18

Warranty:

2 years

Order Description

<i>Order Number</i>	<i>Color</i>	<i>Number of Keys</i>	<i>EAN code</i>
JD-0800EU-2	Black	104+4 Keys	4025112084744

ZF Electronic Systems Pleasant Prairie, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
USA

Phone: 262.942.6500

Internet: www.cherrycorp.com

Sales: 262.942.6500

E-Mail: cep_sales@ZF.com

Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2013 ZF Electronic Systems Pleasant Prairie, LLC
Last update: Feb. 20, 2015