

## Datasheet

### A2, 304 Stainless Steel Self-Colour Hexagon Socket Button Head Screws: Metric Thread

**RS Product No: 1838610**



Button Head Socket Screws are designed for light duty with a similar thread design as a Socket Cap Screw although the dome shaped head is wider and has a lower profile than a Socket Cap Screw, presenting an aesthetic appearance to an assembly.

- A2 grade 304 Stainless Steel
- Threaded in accordance with ISO 7380 standard
- Used for applications with limited space in high tensile applications.
- Suitable for light fastening applications in most food, facilities maintenance and electronic & domestic applications.
- Typical applications include; Machine tooling, Securing guards and covers, Securing ornamental, fixtures, plus many more engineering applications
- Requires a Hex key / Allen key



Professionally approved products.

EN

Please view our full range listing below for all A2, 304 Stainless Steel Self-Colour Hexagon Socket Button Head Screws

Head Shape	Material	Stainless Steel Type	Thread Size	Length	RS Part No.
Hex Socket Button	Stainless Steel	A2, 304	M3	8 mm	1838597
Hex Socket Button	Stainless Steel	A2, 304	M3	10 mm	1838604
Hex Socket Button	Stainless Steel	A2, 304	M3	12 mm	1838610
Hex Socket Button	Stainless Steel	A2, 304	M4	8 mm	1838626
Hex Socket Button	Stainless Steel	A2, 304	M4	10 mm	1838632
Hex Socket Button	Stainless Steel	A2, 304	M4	12 mm	1838648
Hex Socket Button	Stainless Steel	A2, 304	M4	16 mm	1838654
Hex Socket Button	Stainless Steel	A2, 304	M5	10 mm	1838660
Hex Socket Button	Stainless Steel	A2, 304	M5	12 mm	1838676
Hex Socket Button	Stainless Steel	A2, 304	M5	16 mm	1838698
Hex Socket Button	Stainless Steel	A2, 304	M5	20 mm	1838705
Hex Socket Button	Stainless Steel	A2, 304	M5	25 mm	7976092
Hex Socket Button	Stainless Steel	A2, 304	M6	10 mm	7976096
Hex Socket Button	Stainless Steel	A2, 304	M6	12 mm	1838711
Hex Socket Button	Stainless Steel	A2, 304	M6	16 mm	1838727
Hex Socket Button	Stainless Steel	A2, 304	M6	20 mm	1838733
Hex Socket Button	Stainless Steel	A2, 304	M6	25 mm	1838755
Hex Socket Button	Stainless Steel	A2, 304	M6	30 mm	7976106
Hex Socket Button	Stainless Steel	A2, 304	M6	40 mm	7976109
Hex Socket Button	Stainless Steel	A2, 304	M8	12 mm	1838761
Hex Socket Button	Stainless Steel	A2, 304	M8	16 mm	1855794
Hex Socket Button	Stainless Steel	A2, 304	M8	20 mm	1838777
Hex Socket Button	Stainless Steel	A2, 304	M8	25 mm	1838783
Hex Socket Button	Stainless Steel	A2, 304	M8	30 mm	7976103
Hex Socket Button	Stainless Steel	A2, 304	M8	40 mm	7976112
Hex Socket Button	Stainless Steel	A2, 304	M8	50 mm	7976115

