

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002096125

Status:


Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Selective Gold (Au) Plated Brass Contact, 18-22 AWG, Reel



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Specification PS-02-09 \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	1380
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Standard .093" Pin and Socket Connectors
Packaging Alternative	02-09-6126 (Loose)
Product Name	Standard .093"
UPC	800754254625
Physical	
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.206/g
Packaging Type	Reel
Plating min - Mating	1.270µm
Plating min - Termination	0.254µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm²	N/A
Material Info	
Engineering Number	1380591
Reference - Drawing Numbers	
Product Specification	PS-02-09
Sales Drawing	SD-1380-*

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

1380 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	11020003
Extraction Tool	11030006
Terminator Die	11402002
Extractor Tool	638240200
for .093 and HCS-125 Product Series	
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 18 AWG	638280900
Hand Crimp Tool for Standard .093" Pin	638281700

and Socket Crimp
Terminals, 20 AWG
Mini-Mac Applicator 638924000
Mini-Mac Applicator 638927000

This document was generated on 11/26/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION