

## 2-Port Mini DisplayPort to VGA Splitter, TAA

MODEL NUMBER: **B155-002-VGA**



### Description

The B155-002-VGA 2-Port Mini DisplayPort to VGA Splitter converts and splits a Mini DisplayPort video signal for display on two VGA-enabled monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms, this compact splitter features a built-in Mini DisplayPort cable that connects to the source. It lets you use your existing VGA displays instead of buying new Mini DisplayPort monitors or docking stations.

The B155-002-VGA supports video resolutions up to 1920 x 1080 (1080p) at 60 Hz, as well as HDCP, EDID and DDC. Orange LEDs next to each output port indicate whether the splitter is powered on and transmitting a signal to the connected displays. The splitter works with all operating systems and is small enough to carry in your backpack or computer bag. Plug-and-play convenience means no software or drivers are needed. An included USB Micro-B cable connects between the source and the splitter to provide power, so no external power supply is required.

### Features

Converts and Splits Mini DisplayPort Signal to 2 VGA Displays Simultaneously

- Ideal for offices, conference rooms, trade shows and classrooms
- Built-in Mini DisplayPort cable connects to source
- Included USB Micro-B cable supplies power to splitter
- Save money on new Mini DisplayPort displays or docking stations

### Top-Shelf Performance

- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Complies with HDCP, EDID and DDC
- LEDs indicate whether splitter is powered on and transmitting signal to connected displays

### Highlights

- Supports video resolutions up to 1920 x 1080 @ 60 Hz
- Included USB Micro-B cable supplies power to unit
- Works with all operating systems
- Compact enough for easy carrying in backpack or laptop bag
- Plug and play—no software or drivers required

### Package Includes

- B155-002-VGA 2-Port Mini DisplayPort to VGA Splitter
- USB Micro-B cable, 3 ft.
- Owner's manual



#### Easy to Use Almost Anywhere

- Works with all operating systems
- Plug and play—no software, drivers or external power supply required
- Compact unit fits easily in backpack or computer bag

## Specifications

MODEL TEXT	
Key Benefit	Converts and splits a Mini DisplayPort video signal for display on two VGA monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms.
CONNECTIONS	
Ports	2
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>