





## For Patient-Care Vicinity-UL 60601-1 Medical-Grade Power Strip; 4 15A Hospital-Grade Outlets, Safety Covers, 6 ft. Cord

MODEL NUMBER: PS-406-HGULTRA











### Description

The PS-406-HGULTRA Medical-Grade Power Strip is designed with full 60601-1 compliance, making it ideal for use in all patient-care vicinities. This 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

A patented protection circuit guards against shock hazards by preventing power from reaching the unit's outlets in the presence of a fault. The protection circuit automatically resets itself and restores power once the fault threat is gone.

Mounting tabs and flanges let you install the PS-406-HGULTRA on a wide variety of surfaces. The allmetal housing ensures safety and is guaranteed to last a long time in demanding environments.

With a switchless design that prevents accidental shutoff and a 6 ft. power cord that provides some flexibility in placing the power strip, the PS-406-HGULTRA is the perfect replacement for all non-compliant power strips. Patent #7,375,939

#### **Features**

Power Distribution Anywhere in Any Medical Facility

- Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas
- · Patented protection circuit guards against shock hazards
- · Circuit breaker resets itself once fault threat is gone
- 120V, 50/60 Hz power strip complies with UL 60601-1 and UL 60950-1 specifications

#### **Highlights**

- Approved for use in all patientcare vicinities
- Complies with UL 60601-1 and UL 60950-1 specifications
- · Patented protection circuit guards against shock hazards
- 4 NEMA 5-15R-HG hospitalgrade outlets with locking safety
- 6 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Patent # 7.375.939

#### Package Includes

- PS-406-HGULTRA UL 60601-1 Medical-Grade Power Strip
- · Owner's manual with maintenance requirements



• Patent # 7,375,939

Versatile Medical-Grade Solution

- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- 6 ft. power cord provides ample reach to the power source
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Integrated locking outlet safety covers block access to unused outlets
- Built-in 15A circuit breaker protects against dangerous overloads
- · Switchless design prevents accidental shut-off

Ready to Use Right Out of the Box

• Built-in mounting tabs and flanges make the PS-406-HGULTRA easy to install on a variety of surfaces

# **Specifications**

MODEL TEXT		
Key Benefit	Full 60601-1 compliance, integrated locking safety covers and a 6 ft. cord make this medical-grade power strip ideal for all areas inside and outside of patient care vicinities.	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(4) 5-15R-HG	
Circuit Breaker (amps)	15	
Overload Protection	15A resettable circuit breaker	
Outlet Safety Covers	Yes	
Outlet Orientation	Single row of 4	
Right-Angle Outlets	0	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A 120V	
Input Connection Type	NEMA 5-15P-HG	
Input Cord Length (ft.)	6	
Input Cord Length (m)	1.83	
Voltage Compatibility (VAC)	120	





USER INTERFACE, ALERTS & CONTROLS		
Switches	No power switch	
PHYSICAL		
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5	
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4	
Unit Weight (lbs.)	3.2	
Unit Weight (kg)	1.45	
Material of Construction	Metal	
Integrated Keyhole Mounting Tabs	Yes	
Receptacle Color	White	
Color (AC Line Cord)	White	
Outlets Measurement (Center to Center)	92mm	
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 334.01mm	
CERTIFICATIONS		
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>