SIEMENS

Data sheet

6GK1901-1BB20-6AA0

Product type designation Product description

IE FC RJ45 Plug PRO (Push Pull)

RJ45 data connector

IE FC RJ45 PLUG PRO; IP65; FAST CONNECT; IE; RJ45 PUSH PULL PLUG FOR ON-SITE MOUNTING TO IE FC TP CABLE 2X2; (PACKAGING UNIT 1 PLUG)



Suitability for use	Field-assembly connector for push-pull device connection in hi	
	degree of protection	

Transmission rate	
Transfer rate / for Industrial Ethernet	10 Mbit/s, 100 Mbit/s

Interfaces	
Number of electrical connections	
 for Industrial Ethernet FC TP cables 	4
 for network components or terminal equipment 	1
Type of electrical connection	
• for Industrial Ethernet FC TP cables	integrated cut-and-clamp contacts for 4-wire TP FC installation cable
 for network components or terminal equipment 	RJ45 connector (Push Pull device connection)
Type of electrical connection / FastConnect	Yes

Mechanical data	
Material / of the enclosure	plastic
Number of reuses	10
Locking mechanism design	Push-pull

Design, dimensions and weight	
Type of cable outlet	180° cable outlet
Width	22 mm
Height	29 mm
Depth	73 mm
Net weight	68.8 g
Connectable cable cross-section	6.5 8 mm

Permitted ambient conditions	
Ambient temperature	
during operation	-40 +70 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
Chemical resistance / to water	resistant
Protection class IP	IP65/67

Product properties, functions, components / general	
Product feature	
 PoE capability 	Yes
PoE+capability	Yes
• silicon-free	Yes
Product component	
• strain relief	Yes

Standards, specifications, approvals	
Certificate of suitability	
 RoHS conformity 	Yes
UL approval	Yes
• cULus approval	No
 Railway application in accordance with EN 50155 	No
Standard for structured cabling	Cat5

• to website: CAx Download Manager

Internet-	l ink
IIIICIIICI-	

• to website: Selector SIMATIC NET http://www.siemens.com/snst **SELECTION TOOL**

http://www.siemens.com/simatic-net • to website: Industrial communication

https://mall.industry.siemens.com • to website: Industry Mall

http://www.siemens.com/industry/infocenter • to website: Information and Download Center

http://automation.siemens.com/bilddb • to website: Image database http://www.siemens.com/cax

https://support.industry.siemens.com • to website: Industry Online Support

07/08/2016 last modified: