# EK2.5-4P



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks Accessories + End Sections

#### **General Information**

Extended Product Type: EK2.5-4P

**Product ID**: 1SNK705912R0000 **EAN**: 3472597059124

Catalog Description: EK2.5-4P End Section - Dark Grey

Long Description: - Unique dark grey color that fits all terminal blocks colours and ease the id

entification of circuits within your terminal block assemblies, - Compatible with ZK2.5-4P, ZK2.5-PE-4P, ZK4-4P and ZK4-PE-4P PI-Spring screwless

terminal blocks.

## Ordering

| Color:                  | Dark Grey |
|-------------------------|-----------|
| Minimum Order Quantity: | 20 piece  |
| Customs Tariff Number:  | 39269097  |

## Popular Downloads

Data Sheet, Technical Information: 1SNK160027C0201
Instructions and Manuals: 1SNK160027C0201

### **Dimensions**

| Product Net Width:          | 2 mm    |
|-----------------------------|---------|
| Product Net Height:         | 82.8 mm |
| Product Net Depth / Length: | 32.8 mm |
| Product Net Weight:         | 2.7 g   |

#### **Technical**

| Spacing:              | 2 mm   |
|-----------------------|--|
| Function:             | End Sections   |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material:  | Polyamide  |
| Mounting on DIN Rail: | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715             |
|                       | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715       |
|                       | TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715         |
|                       | TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715       |
|                       |  |

Suitable For: ZK2.5-4P

ZK2.5-PE-4P

ZK4-4P ZK4-PE-4P

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C

Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230535F0201

Classifications

Object Classification Code: X

**Container Information** 

Package Level 1 Units: 20 piece

Package Level 1 Width: 130 mm

Package Level 1 Depth / Length: 280 mm

Package Level 1 Height: 0 mm

Package Level 1 Gross Weight: 0.074 kg

Package Level 1 EAN: 3472597059124

Package Level 2 Units: 1800 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 300 mm

Package Level 2 Height: 400 mm

Package Level 3 Units: 10800 piece

Product Packing Type: Bag

