LINE VOLTAGE THERMOSTATS / WIRELESS REMOTE SENSOR

White-Rodgers™

LINE VOLTAGE THERMOSTATS FOR HEATING

For Control of Most Line Voltage Heating Applications without Use of Relays or Motor Starters

FEATURES

- "Summer" dial position (152-9 model)
- Heavy gauge steel case – Mounts on vertical 2″ x 4″ box or flush to wall.
- Hydraulic action element – Unaffected by motion – No leveling required.
- Dustproof case.

SPECIFICATIONS

Dimensions. . . . . 4$\frac{1}{2}$″H x 4$\frac{1}{2}$″W x 2$\frac{1}{4}$″D
Agency . . . . U.L. listed and C.S.A. approved

152-9

PARTS AND ACCESSORIES See end of thermostats section for additional parts and accessories

- Thermostat Guards — see pages 34–35

Model Number	Range	Differential	Action	Full Electrical Rating	Motor Rating (Full Load)		Motor Rating (Non-Inductive)		
					120 VAC	240 VAC	120 VAC	240 VAC	277 VAC
152-9*	55 to 85°F (13 to 29°C)	Fixed 2°F (1.0°C)	Open on Rise	FG See page 222	14.0A	7.0A	25.0A	22.0A	18.0A
152-10**	40 to 90°F (4 to 32°C)	Fixed 3°F (1.6°C)	Open on Rise	FG See page 222	14.0A	7.0A	25.0A	20.0A	–

* Summer fan position control only has two terminals. It thermostatically cycles (based on temperature) unless set to the summer fan position in which case the contacts are closed.

**Locked case,concealed dial.

WIRELESS REMOTE SENSORS FOR 1F98EZ-1621 WIRELESS THERMOSTAT SYSTEM

Wireless Indoor and Outdoor Sensors for use with 1F98EZ-1621 Emerson Blue Wireless Easy Install Thermostat System

FEATURES

- Up to 3 indoor and 1 outdoor wireless remote sensors can be used on one 1F98EZ-1621 wireless thermostat system.
- Battery powered with 2 "AA" alkaline batteries

F145RF-1600 Wireless Remote Sensor

SPECIFICATIONS

Operating Temperature Range . . . . 0° to 120°F (-18° to 49°C)
Battery . . . . 2 "AA" Alkaline Batteries
Operating Humidity Range . . . . 0 to 85% RH (non-condensing)
Color . . . . Classic White
Weight . . . . Weighs less than 0.25 lb
Dimension . . . . 4$\frac{1}{2}$″H x 3$\frac{1}{4}$″W x 1$\frac{1}{2}$″D
Maximum Distance from Interface . . . . 300′

PARTS AND ACCESSORIES See end of thermostats section for additional parts and accessories

- Thermostat Guards — see pages 34–35

WIRELESS REMOTE SENSOR (INDOOR OR OUTDOOR

Model Number	Color	Dimensions	Application
F145RF-1600	Classic White	4$\frac{1}{2}$″ x 3$\frac{1}{4}$″ x 1$\frac{1}{2}$″	Compatible with Emerson Blue Wireless Easy Install Thermostat System