



Actual

Catalog Number: 2IH5S2-1
Product ID: 7TAA002270R0000
UPC Number: 04226939394
EAN Number: 05414363936398
Status: Active

Two Gang Universal Weatherproof Box, 31.8 Cubic Inches, Hub Size 1/2 Inch, Silver, Aluminum, 5 Outlets (2-Sides) with 1 on Top, Bottom, Both Sides, and Back

- Alloy A380 aluminum, certified zinc alloy and stainless steel springs provide increased corrosion resistance
- Die Cast construction and industrial design combine to produce a rugged protective enclosure for devices.
- Clean cover edges provide good gasket sealing.
- Precision cast and machined surfaces permit safer wire pulling.
- Clear UL and cubic content markings speed approval by inspectors
- Convenient mounting lugs for a variety of mounting methods
- Securely fastened mounting plates reduce costly call backs

North American Specifications (UNSPSC)

UNSPSC	39121305 Weatherproof boxes
IGCC	4429 Weatherproof boxes
Brand Name	Red Dot
Type	Device Boxes, Covers & Accessories
Special Features	Alloy A380 aluminum, certified zinc alloy and stainless steel springs provide increased corrosion resistance
Application	Dry-tite boxes and covers protect wiring devices, switches, electronic components and terminal blocks in dry, damp and wet locations
Standard	UL E28688
Number Of Outlet	5
Material	Aluminum Die Cast
Color	Silver
Cubic Capacity	31.8

European Specifications (ETIM)

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Rectangular
Construction type	Device connection box (round/square)
Equipped with	None
Length	115.8748mm
Width	117.475mm
Depth	52.3748-52.3748mm
Mounting switching equipment	Screwing
With screws	N
Pipe locking	N
Pipe locking optional	N
Inlet from the rear	Y
Number of inlets	5
Material	Other
Colour	Other
Cover	None

Cover attachment	Not applicable
Sealable	N

Packaging

Inner Quantity	1
Inner Dimensions (inches)	4.75x4.63x2.13
Outer Quantity	10
Outer Dimensions (inches)	10.7x10x5.3
Weight Uom	95 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Catalog US 1	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com