

2-Port USB to DB9 Serial FTDI Adapter Cable with COM Retention (M/M), 6 ft.

MODEL NUMBER: **U209-006-2**



Description

The U209-006-2 2-Port USB to DB9 Serial FTDI Adapter Cable (M/M) allows you to connect two 9-pin RS-232 serial peripherals to a device with a USB-A port. Recommended for connecting a modem, digital camera, PDA or ISDN terminal to your computer, laptop or tablet, this cable supports data transfer speeds up to 225 Kbps—basically twice as fast as a built-in serial port. No external power source is required. The compact six-foot cable tucks away in your backpack or laptop bag for use anywhere.

The hot-swappable U209-006-2 with built-in FTDI FT232RL chipset offers COM retention. It automatically reassigns the same COM port values to each port in case the cable is disconnected or the system is rebooted.

Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. Works with Windows, Mac and Linux computers.

Features

Connects 2 DB9 Devices to a USB-A Device

- Recommended for connecting a modem, digital camera, PDA or ISDN terminal to your computer, laptop or tablet
- Supports data transfer speeds up to 225 Kbps—twice as fast as a built-in serial port
- No external power source required
- Portable 6 ft. design fits perfectly into laptop bag
- COM retention for automatic reassigning of COM values to ports in case of disconnection or reboot
- Integrated FTDI FT232RL chipset

Highlights

- Supports data transfer speeds up to 225 Kbps
- Premium foil and braid shielding reduces EMI/RFI line noise
- Compatible with Windows®, Mac® and Linux® devices
- No external power source required
- Integrated FTDI FT232RL chipset

System Requirements

- Computer or other device with available USB port and Windows XP or later, Mac OS X 10.3 and later, or Linux operating system

Package Includes

- U209-006-2 2-Port USB to DB9 Serial FTDI Adapter Cable (M/M), 6 ft.
- Driver CD
- Owner's manual



First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors with gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jacket easy to install in tight spaces

Broad Compatibility

- Compatible with Windows, Mac and Linux operating systems

Specifications

MODEL TEXT	
Key Benefit	Connect 2 devices with 9-pin RS-232 serial ports to the USB-A port on your computer, laptop or tablet. Recommended for connecting modems, digital cameras, PDAs and ISDN terminals.
INPUT	
Cable Length (ft.)	6
Cable Length (m)	2
PHYSICAL	
Color	Black
CONNECTIONS	
Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) DB9 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>