

APC Back-UPS™

Technical Specifications

Extended runtime for high and low power devices

- Wireless router
- Broadband modem
- Mobile devices
- Desktop Computer (PC)
- External monitor
- Voice-over IP (VOIP) phone
- Wi-Fi home security camera
- Structured wiring closet
- Television
- Security system
- Automation hub
- Gaming console



	BE425M	BE600M1	BE850M2
Runtime			
Internet modem and router (10 watts)	2.3 hours	4.3 hours	5.9 hours
Entry level PC (40 watts)	45 minutes	67 minutes	90 minutes
Notebook computer + network gateway (80 watts)	18 minutes	30 minutes	41 minutes
Midrange PC with 20" LCD + Notebook + network gateway (180 watts)	5.8 minutes	10 minutes	14.8 minutes
Output			
Output Capacity	425 VA, 255 Watts	600 VA, 330 Watts	850 VA, 450 Watts
Output Voltage / Frequency (On utility)	115 Vac +/- 8%		
Output Voltage / Frequency (On battery)	50 or 60 Hz +/- 1Hz autosensing		
Output Connections	6 NEMA 5-15 outlets 4 battery backup outlets 2 surge only outlets	7 NEMA 5-15 outlets 5 battery backup outlets 2 surge only outlets	9 NEMA 5-15 outlets 6 battery backup outlets 3 surge only outlets
Waveform Type	Simulated Sine Wave		
Surge Protection			
AC Power Surge Protection	All Outlets		
Circuit Breaker	7 A	15 A	15A
AC Input	Resettable Circuit Breaker		
Input			
Maximum Adjustable Input Voltage	88-142 Vac		
Frequency	47-63 Hz		
Input Voltage Range	92-139 Vac (medium sensitivity, default); 88-142 Vac (low sensitivity); 96-136 Vac (high sensitivity)		
Input Connection	5 ft. (1.52 meter) line cord with NEMA 5-15 right angle plug		
Physical			
Color	Black		
Dimensions (HxWxD)	5.51" x 4.13" x 9.96" (14.0 cm x 10.5 cm x 25.3 cm)	5.47" x 4.13" x 10.79" (13.9 cm x 10.5 cm x 27.4 cm)	5.47" x 4.13" x 12.87" (13.9 cm x 10.5 cm x 32.7 cm)
Weight	5.72 lb (2.6 kg)	7.5 lb (3.4 kg)	9.02 lb (4.1 kg)
USB Charging Port			
USB Charger Output	N/A	7.5W / 5V / 1.5A	12W / 5V / 2.4A
USB Charger Type	N/A	1-USB A-Type	2-USB A-Type
Compatibility	N/A	USB charging specification 1.2	USB charging specification 1.2
Management			
Alarms	Audio and Visual Indicators		
Software	NA	PowerChute Personal Edition V3.0.2	
Warranty	3 years		