

## 4-Port USB Charging Station, 5V 6A/30W USB Charger Output, UK Version

MODEL NUMBER: **U280-004-UK**



### Description

Whether you're at home or in the office, Tripp Lite's U280-004-UK 4-Port USB Charging Station provides enough ports and power to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to four tablets, cell phones, laptops and other devices at the same time. The U280-004-UK doesn't require a computer, so you can take it anywhere AC power is available.

The U280-004-UK simultaneously provides up to 5V, 1.5A of power per port at maximum capacity. Each individual port is capable of delivering up to 5V, 2.4A, which is enough for charging even battery-intensive devices like the Apple® iPad®.

To charge your USB devices, simply connect the 1.2-meter power cord's BS-1363 plug to an AC power outlet, and connect your devices to the available USB ports. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power.

### Features

#### Charges Up to 4 Devices at the Same Time

- Ideal for charging tablets, cell phones, laptops and other devices at home or work
- Connect devices to unit's USB ports for proficient charging
- Functions anywhere AC power is available—no computer required

#### Provides Plenty of Juice for Charging

- Each individual port capable of delivering up to 5V, 2.4A, enough for charging battery-intensive devices like the Apple iPad

### Highlights

- 5V, 2.4A per port for charging battery-intensive devices
- 5V, 1.5A per port simultaneously when at maximum capacity
- Internal dual-voltage power supply with BS-1363 plug
- Protects against overheating, overcurrent and overcharging
- No computer required

### Package Includes

- U280-004-UK 4-Port USB Charging Station
- C7 to BS-1363 power cord, 1.2 m
- Quick Start Guide



- Simultaneously provides up to 5V, 1.5A of power per port at maximum capacity
- Protects against overheating, overcurrent and overcharging

#### Easy to Use

- 1.2 m power cord with BS-1363 plug connects to AC outlet
- Front LED indicates when unit is turned on and receiving AC power

## Specifications

MODEL TEXT	
Key Benefit	Charges up to 4 electronic devices at the same time via USB connection. Ideal for quick-charging tablets, cell phones, laptops and other mobile devices.
OUTPUT	
Charging Ports / Amps	(4) 2.4A
Charging Method	USB
PHYSICAL	
Unit Dimensions (hwd / in.)	1.2 x 4.2 x 4.0
Unit Dimensions (hwd / cm)	3.1 x 10.6 x 10.1
Unit Weight (lbs.)	0.46
Unit Weight (kg)	0.21
Color	White
ENVIRONMENTAL	
Operating Temperature Range	41°F to 95°F / 5°C to 35°C
Storage Temperature Range	-4°F to 122°F / -20°C to 50°C
Relative Humidity	20% to 80%
CERTIFICATIONS	
Approvals	UL Listed
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>