

## FC to LC 62.5/125 Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-LC62**



### Description

The T020-001-LC62 FC to LC 10 Gb Adapter converts a native FC fiber female port on the Tripp Lite [T020-001-PSF](#) Multi-Function Optical Fiber Cable Tester to an LC female port for 62.5/125 multimode cable testing. "62.5/125" is clearly labeled on the unit to differentiate the T020-001-LC62 from other adapters. Included dust caps keep the connectors clean when not in use.

### Features

Converts Cable Tester's FC Connector to an LC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 62.5/125 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with [T020-001-PSF](#) Multi-Function Optical Fiber Cable Tester

## Specifications

| MODEL TEXT    |   |
|---------------|---|
| Key Benefit   | Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an LC connector. Ideal for cable installers or anyone else working in telecom or LAN environments. |
| OVERVIEW      |   |
| Clad Diameter | 125   |
| Core Diameter | 62.5  |

### Highlights

- Converts native FC jack to an LC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 62.5/125 multimode cable testing
- Included dust caps keep connectors clean
- For use with [T020-001-PSF](#) Optical Fiber Cable Tester

### System Requirements

- Tripp Lite T020-001-PSF Multi-Function Optical Fiber Cable Tester

### Package Includes

- T020-001-LC62 FC to LC 62.5/125 Adapter



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| <b>PHYSICAL</b>                     |                           |
| Color                               | Beige; Silver             |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>