

# DK6 : 5/6" LED Downlight Kit



project name	type
catalog number	
comments	voltage
approved by	date

11/15  
watts

700/  
1100  
lumens

90+  
CRI

2700K-  
5000K  
CCT

## Features

- Ultra-efficient LED Downlight Kit designed to retrofit into existing incandescent recessed downlights
- Integrated LEDs reduce energy consumption up to 80%
- Fits many popular 5" & 6" recessed downlight fixtures
- Integrated white trim with medium base (E26) for direct replacement
- Dimmable 10-100%
- Lasts up to 30X longer than traditional incandescent
- Choice of warm white or cool white color temperatures
- Instant-on, no warm-up time

## Performance

- 11W 700lm equivalent to 65W BR incandescent
- 15W 1,100lm equivalent to 90W BR incandescent
- Long life: 50,000+ hours
- Rated for Damp and Wet Locations
- CRI: >90
- 120V @ 60hz
- ENERGY STAR® Approved

## Applications

- Healthcare
- Hospitality
- Office
- Property Management
- Residential
- Retail

## Ordering Information

Order Code	Item #	Lm	W	CCT	CRI	MOL	Life/Hrs	Replaces Incan.	ENERGY STAR
09681	LED-DK6-11W927-DIM-G7	700	11W	2700K	90+		50,000	65W BR	★
09682	LED-DK6-11W930-DIM-G7	700	11W	3000K	90+		50,000	65W BR	★
09683	LED-DK6-11W940-DIM-G7	700	11W	4000K	90+		50,000	65W BR	★
09684	LED-DK6-11W950-DIM-G7	700	11W	5000K	90+		50,000	65W BR	★
09685	LED-DK6-15W927-DIM-G7	1100	15W	2700K	90+		50,000	90W BR	★
09686	LED-DK6-15W930-DIM-G7	1100	15W	3000K	90+		50,000	90W BR	★
09687	LED-DK6-15W940-DIM-G7	1100	15W	4000K	90+		50,000	90W BR	★
09688	LED-DK6-15W950-DIM-G7	1100	15W	5000K	90+		50,000	90W BR	★

★ ENERGY STAR® Approved




RoHS Compliant



# DK6 : 5/6" LED Downlight Kit

## Spectral Flux



watch > like > follow



23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 · (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 · (F) 1.888.705.1335