

Monitor - BL FPM 15.6 - 2402980

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



IP65-rated, 15.6-inch, flat -panel LCD monitor with projective capacitive touch screen

Product Description


The Baseline BL FPM 15.6 is an industrial flat-panel monitor that can be used in applications where a remote display location is required.

Why buy this product

- 15.6-inch display
- DisplayPort 1.2, VGA, and DVI-I input ports
- Integrated configuration buttons
- Ambient operating temperatures from -10°C to 60°C
- 15.6-inch touch screen display



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 202297
GTIN	4055626202297

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Display

Display	39.6 cm/15.6" TFT
Screen resolution	1366 x 768 Pixel(s) (WXGA)
Backlighting	LED
Display backlight MTBF	> 50000 h
Touch technology	projective-capacitive, ten-touch control
Colors	16.7 million colors

Monitor - BL FPM 15.6 - 2402980

Technical data

Monitor data

Network	Without network
Interfaces	1x USB 1.1, Typ A
	1x USB 2.0, Typ A
Monitor output	1x DisplayPort
	1x DVI-D
	1x VGA
Slots	without slots
Optical drive	without drive

General

Mounting type	VESA MIS-D, 100
	Front installation
Weight	5.48 kg

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Vibration (operation)	1g
Shock	15g, 11 ms impulse

Device supply

Supply voltage	24 V DC (±20%)
Power supply unit	24 V DC

Standards and Regulations

Shock	15g, 11 ms impulse
Vibration (operation)	1g

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals


UL Listed / cUL Listed / cULus Listed


Monitor - BL FPM 15.6 - 2402980


Approvals

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	---	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	---	---	---------------

cULus Listed			
--------------	---	--	--

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>