## **Minim<sup>®</sup> & Maxim<sup>®</sup>** Self-Adjusting Wire Strippers

Reliable and comfortable

**Heavy duty,** self adjusting wire stripping and cutting tool. Ergonomic handle is designed for comfort and reduces fatigue. The auto form laminated stripping jaws form around the radius of the cable to ensure no damage to the inner conductor.

- Set adjustable wire stop for precise strip lengths.
- High leverage built-in cutter with safety guard.
- Made of high grade polymers and carbon steels to ensure long life and reliable performance.

## **Technical / Features**

For use with PVC insulated wires and cables, solid or stranded:

- Maxim<sup>®</sup> 6:
  - 0.2 6mm SQ
  - 24-10 AWG stripping range
  - 30-10 AWG cutting range
- Maxim<sup>®</sup> 16:
  - 6 16mm SQ
  - 10-5 AWG stripping range
  - 10-5 AWG cutting range
- Minim<sup>®</sup> 2.5:
  - 0.2 2.5mm SQ
  - 30-13 AWG stripping range
  - 30-13 AWG cutting range

Phone: 800.749.5783 Fax: 800.749.5784

California, USA

www.platinumtools.com

We Make Connections EZ!

©2015 Platinum Tools, Inc. All rights reserved, PF-Minim/M

## Minum<sup>®</sup> and Maxim<sup>®</sup> Self-Adjusing Wire Strippers



Wire Cutter with safety guard



Wire Stop for precise strip length




Replacement Blade Cassettes for all three models



- Maxim<sup>®</sup> 6 and Maxim<sup>®</sup> 16: - 8" x 4" x 3/4" (205x105x19 mm) Weight: 7 ex (200 c)
  - Weight: 7 oz (200 g)
- Minim<sup>®</sup> 2.5:
  - 4" x 5" x 11/16 (104x130x17mm)
  - Weight: 5.5 oz (156 g)



Maxim<sup>®</sup> 6 - 24-10 AWG stripping range - 30-10 AWG cutting range



Laminated Blades



Maxim<sup>®</sup> 16 - 10-5 AWG stripping range - 10-5 AWG cutting range



Ordering Information	
Description	P/N
Maxim <sup>®</sup> 6 Self-Adjusting Wire Stripper 24-10 AWG	15310C
Maxim <sup>®</sup> 16 Self-Adjusting Wire Stripper 10-5 AWG	15316
Minim <sup>®</sup> 2.5 Self-Adjusting Wire Stripper 30-13 AWG	15305C
Replacement Blade Cassette for Maxim <sup>®</sup> 6	15313C
Replacement Blade Cassette for Maxim <sup>®</sup> 16	15317
Replacement Blade Cassette for Minim <sup>®</sup> 2.5	15308C