

# 2440

## Brand Features

Leviton's Industrial Grade Locking Devices are built to provide unparalleled quality and superior performance in the most severe industrial settings. Leviton combines the best materials available with superior production standards to produce a broad selection of Locking Devices of unmatched flexibility and dependability.

## Item Description

20 Amp, 120/208 Volt 3-Phase Y, NEMA L18-20R, 4P, 4W, Flush Mtg Locking Receptacle, Industrial Grade, Non-Grounding, V-0-MAX - BLACK

## Technical Information

### AC Horsepower Ratings

**At Rated Voltage:** 2 HP

### Electrical Specifications

**Amperage:** 20 Amp

**Current Limiting:** Full Rated Current

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Non-Grounding

**Pole:** 4

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

**Voltage:** 120/208 Volt 3-Phase Y

**Wire:** 4

### Environmental Specifications

**Environment:** Corrosive

**Flammability:** Rated V-0 per UL94

**Operating Temperature:** -40C to 60C

### Material Specifications

**Base Material:** Valox

**Body Material:** Nylon

**Color:** Black

**Cover Material:** Valox 357

**Face Material:** Ultramid

**Ground Contacts:** Brass

**Grounding Screw:** Chromated Brass

**Line Contacts:** Brass

**Strap Material:** Nickel-Plated Brass

**Terminal Clamps:** Nickel-Plated Brass

**Terminal Screws:** Chromated Brass

### Mechanical Specifications

**Product ID:** Ratings and NEMA I.D. permanently marked on device

**Terminal Accom.:** 14-8 AWG

**Terminal ID:** Marked on Device

**Termination:** Back & Side

### Product Features

**Base Material:** Valox

**Brand:** V-0-Max

**Color:** Black

**Device Type:** Locking Receptacle

**Face Material:** Ultramid

**NEMA:** L18-20R

**Voltage:** 120/208 Volt 3-Phase Y

**Warranty:** Lifetime Limited

### Standards and Certifications

**ANSI:** C-73

**CSA:** C22.2 No. 42

**NEMA:** WD-1 & WD-6

**NOM:** 057

**UL:** 498

**UL Fed Spec:** W-C-596

**Warranty:** Lifetime Limited



**Color:** Black




**UPC Code:** 07847704534

**Country Of Origin:** Mexico


**NEMA:**  
L18-20R



### Dimensional Diagram



### Wiring Diagram



### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

