

NOTES:

1. MATERIALS AND FINISHES:

REVERSE POLARITY SMA BULKHEAD CRIMP JACK IP 67 - P/N: 132422RP-10
 MICRO COAX RIGHT ANGLE PLUG TERMINATED USING 1.13 MM CABLE - P/N: A-1PA-113-XXXB2

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM, NOMINAL



3. PACKAGING:

A. QUANTITY: SINGLE PACK
 B. BAG TO BE MARKED: AMPHENOL RF, 336320-12-XXXX, AND DATE CODE

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	17-Dec-14	2838	CL/BCG
B	ADD 400MM LENGTH, UPDATE LAYOUT	19-Mar-18	07361	KCE
C	ADD 350MM LENGTH	23-May-18	8161	NB



AMPHENOL RF PN	CABLE LENGTH (IN)	CABLE LENGTH (MM)
336320-12-0050	1.968±0.150	50±3.81
336320-12-0100	3.936±0.150	100±3.81
336320-12-0150	5.905±0.150	150±3.81
336320-12-0200	7.873±0.200	200±5.08
336320-12-0250	9.842±0.200	250±5.08
336320-12-0300	11.810±0.200	300±5.08
336320-12-0350	13.780±0.200	350±5.08
336320-12-0400	15.748±0.200	400±5.08

* ADDITIONAL LENGTHS CAN BE PROVIDED.
 CONTACT AMPHENOL RF MARKETING FOR QUOTE

DESIGN REQUIREMENTS:

- | | |
|--|--|
| <input checked="" type="checkbox"/> FREQUENCY: DC TO 6 GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input type="checkbox"/> VSWR _____ : 1 MAX | <input checked="" type="checkbox"/> HI-POT :200 VRMS |
| <input type="checkbox"/> INS. LOSS _____ dB MAX | <input type="checkbox"/> OTHER |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
 <0.5mm ±0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	DRAWN	DATE	TITLE	Amphenol RF www.amphenolrf.com DRAWING NO. 336320-12-XXXX ITEM NO. 336320-12-XXXX PART NO. 336320-12-XXXX
REFERENCE	CLEMENT	18-Nov-14	REVERSE POLARITY SMA BULKHEAD CRIMP JACK IP 67 TO AMC RIGHT ANGLE PLUG TERMINATED USING 1.13 MM CABLE, VARIOUS LENGTHS	
EAR# 6511	ENGINEER	DATE	SCALE: 5.0:1.0 SHEET 2 OF 2	
REF:	CLEMENT	18-Nov-14	DWG SIZE B REV C	
CONFIGURATION LEVEL: In Work	APPROVED	DATE		
FINISH	K. CAPOZZI	23-May-18		
	CAD FILE			

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY