

USB 3.0 Docking Station for Microsoft Surface and Surface Pro, USB-A and Gigabit Ethernet Ports

MODEL NUMBER: **U342-GU3**



Description

The U342-GU3 USB 3.0 Docking Station expands the capabilities of your Microsoft® Surface® or Surface Pro by adding Gigabit Ethernet access and up to three USB peripherals, such as a printer, scanner and external hard drive. It's compatible with all Surface models and versions. Its built-in stretching bracket allows it to fit perfectly on the Surface kickstand. No software or drivers are needed.

Access a 10/100/1000 Mbps wired network without an internal Ethernet card. The RJ45 Gigabit Ethernet connection complies with IEEE 802.3, 802.3u and 802.3ab standards and supports IEEE 802.3az Energy Efficient Ethernet, as well as full- and half-duplex operations, Wake-on-LAN, jumbo frames, VLAN tagging and auto-MDIX. It also supports Checksum Offload Engine (COE) to reduce CPU loading.

The USB 3.0 ports achieve data transfer speeds up to 5 Gbps without compromising signal quality. They're backward compatible with previous USB generations.

Features

Compatible with All Surface Models and Versions

- Plug and play with no software or drivers needed
- Fits perfectly on Surface kickstand
- Recommended for accessing a Gigabit Ethernet LAN, transferring data or connecting a printer or scanner

Add Up to 3 USB-A Devices to Your Surface

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Backward compatible with previous USB generations

Highlights

- Supports data transfer rates up to 5 Gbps
- Ensures true 10/100/1000 Mbps Ethernet network speeds
- Fits perfectly on Surface kickstand
- Backward compatible with previous USB generations
- Plug and play with no software or drivers needed

System Requirements

- Any model Microsoft Surface or Surface Pro

Package Includes

- U342-GU3 USB 3.0 Docking Station
- External Power Supply with 1-15P Plug (Input: 100–240V, 50/60 Hz, 0.4A Max; Output: 5V, 2A)
- Owner's manual



Join a Wired Gigabit Ethernet Network

- Ensures true 10/100/1000 Mbps Ethernet network speeds
- Complies with IEEE 802.3, 802.3u, 802.3ab and 802.3az standards
- Supports full- and half-duplex, Wake-on-LAN, jumbo frames, VLAN tagging and auto-MDIX
- Supports IPv4/IPv6 COE to reduce CPU loading

Specifications

MODEL TEXT	
Key Benefit	Adds 3 USB 3.0 ports and an RJ45 Gigabit Ethernet jack to your Microsoft Surface or Surface Pro. Recommended for transferring photos and other data, joining Ethernet networks or accessing printers and scanners.
OVERVIEW	
AC Adapter	Input: 100V-240V, 50/60Hz, 0.4A Max Output: 5V 2A
Dock Connectors	3 x USB3.0, RJ45 LAN
Accessories Type	Converter
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side A - Connector 2	(3) USB 3.0 A (FEMALE)
PC/Server Connections	USB
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>