

4K Video and Ethernet 3-in-1 Accessory Kit for Microsoft Surface and Surface Pro

MODEL NUMBER: P137-GHV-V2-K2



Description

The P137-GHV-V2-K2 4K Video and Ethernet 3-in-1 Accessory Kit expands the capabilities of your Microsoft® Surface® or Surface Pro by adding Gigabit Ethernet access and an external 4K HDMI or VGA monitor. These three lightweight, low-profile adapters fit neatly into your backpack or laptop bag, so you can use them anywhere you take your Surface product.

For displaying videos, spreadsheets, documents and presentations on a larger screen, the Mini DisplayPort™ to VGA adapter allows connection to a VGA-enabled monitor at resolutions up to 1920 x 1200, including 1080p. Or use the Mini DisplayPort to HDMI adapter to connect to a 4K-enabled television, monitor or projector at UHD resolutions up to 3840 x 2160 (@ 24/30 Hz).

The USB 3.0 SuperSpeed to Gigabit Ethernet adapter allows your Surface to access a 10/100/1000 Mbps wired network without an internal Ethernet card. It achieves USB 3.0 data transfer speeds up to 5 Gbps without compromising signal quality. It complies with IEEE 802.3 (10Base-T) and 802.3u (100Base-TX) standards and supports IEEE 802.3az Energy Efficient Ethernet, as well as full- and half-duplex operations, suspend mode and remote wakeup via link-up, and magic packet.

Features

Mini DisplayPort to VGA Adapter

- Connects your Surface to a VGA display
- Supports VGA video resolutions up to 1920 x 1200

Mini DisplayPort to HDMI Adapter

- Connects your Surface to an HDMI display
- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz

Highlights

- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports VGA video resolutions up to 1920 x 1200 (1080p)
- Ensures true 10/100/1000 Mbps Ethernet network speeds
- Plug and play with no external power supply needed
- Small enough to carry easily in laptop bag or backpack

Package Includes

- Mini DisplayPort to VGA adapter (M/F)
- Mini DisplayPort to HDMI adapter (M/F)
- USB 3.0 SuperSpeed to Gigabit Ethernet adapter (M/F)
- Driver CD for Ethernet adapter
- Owner's manual for Ethernet adapter



USB 3.0 SuperSpeed to Gigabit Ethernet Adapter

- Connects your Surface to a wired Ethernet network
- Ensures true 10/100/1000 Mbps network speeds
- Reaches USB 3.0 data transfer speeds up to 5 Gbps
- Complies with IEEE 802.3, 802.3u, 802.3ab and 802.3az standards
- Supports full- and half-duplex, suspend mode and remote wakeup via link-up, and magic packet

Plug and Play Operation

- No external power supply needed
- Small enough to carry easily in laptop bag or backpack
- Compatible with Microsoft Surface and Surface Pro

Specifications

MODEL TEXT	
Key Benefit	Adds Gigabit Ethernet access and an external 4K HDMI or VGA monitor to your Microsoft Surface or Surface Pro.
OVERVIEW	
Accessories Type	Adapter
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	Black; White
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side A - Connector 2	MINI DISPLAYPORT (FEMALE)
Side A - Connector 3	USB 3.0 A (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	RJ45 (FEMALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>