

Keyspan Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F), 1920 x 1200 (1080p) @ 60 Hz

MODEL NUMBER: **P139-000-DP**



Connects a computer with a Mini DisplayPort (mDP) output to a high-definition monitor, projector or television with a DisplayPort™ input. Recommended for use with Microsoft Surface.

Description

The P139-000-DP Keyspan® Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F) connects your existing mDP device to a high-definition DisplayPort monitor, projector or television. By converting the mDP connector to DisplayPort, the P139-000-DP allows you to continue using your existing DisplayPort display instead of buying a new Mini DisplayPort monitor.

Recommended for laptops, tablets and Microsoft Surface devices, the P139-000-DP is ideal for displaying crystal-clear video on a large monitor or digital sign. It supports high-definition video resolutions up to 1920 x 1200, including 1080p, at 60 Hz. The compact one-piece molded adapter is designed to go where you go. It fits into your pocket, purse, or laptop bag, allowing you to quickly connect your computer to a DisplayPort display using your regular DisplayPort cable.

Compliant with HDCP 2.2 and DisplayPort 1.2. Plug-and-play design requires no software or drivers.

Features

Sends Mini DisplayPort Audio/Video to a DisplayPort Display

- Connects an mDP computer to a DisplayPort monitor, projector or TV
- Ideal for displaying Mini DisplayPort video on a large monitor or digital sign
- Allows you to continue using an existing DisplayPort display, instead of buying a new monitor
- Recommended for laptops, tablets and Microsoft Surface devices

Vibrant Video Quality

Highlights

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz
- Compliant with HDCP 2.2 and DisplayPort 1.2
- Compact 1-piece molded design is easy to carry
- Ideal for laptops, tablets and Microsoft Surface devices
- Plug and play—no software or drivers required

System Requirements

- Source device with Mini DisplayPort connector
- Display device with DisplayPort connector

Package Includes

- P139-000-DP Keyspan Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports HD video resolutions up to 1920 x 1200, including 1080p, @ 60 Hz
- Compliant with HDCP 2.2 and DisplayPort 1.2

Superior Design for Superior Performance

- Compact 1-piece molded design easy to carry in pocket or purse for quick connection anywhere
- Plug and play—no software or drivers required

Specifications

OVERVIEW	
UPC Code	037332205773
Technology	DisplayPort
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.02
Shipping Weight (kg)	0.01
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	0% TO 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>