


## UK BS-1363 Medical-Grade Power Strip with 6 UK Outlets, 3m Cord

MODEL NUMBER: PS610HGUK



Distributes power to plug-connected components inside and outside patient-care vicinities, including examining rooms.

### Features

#### Power Distribution Anywhere in Any Medical Facility

This 230V, 50/60 Hz medical-grade power strip supplies electricity to plug-connected components in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with BS-1363 specifications, the PS610HGUK features a three-meter (10-foot) UK power cord with 13A fused Type G plug and six UK outlets.

#### Armed with the Latest Safety Features to Protect Valuable Equipment

A built-in replaceable 13A fuse controls all six outlets and protects against overloads by shutting them down if the equipment load draws too much power. The switchless design prevents the unit from being accidentally shut off, which would cut essential power to all connected devices. A green mains indicator lights to signal the power strip is properly connected to an AC power source.

#### Long Cord Provides Enhanced Mobility

The three-meter UK power cord allows for optimum flexibility when putting together a mobile health care workstation. The PS610HGUK can be mounted in a different area—or a completely different room—from where it draws AC power, putting you in control of getting reliable power service where you need it most. For best performance, connect the Type G plug to a standard 13A isolated ground receptacle with an isolated earth to eliminate unwanted ground noise.

#### Equipotential Grounding Helps Your Equipment Perform at Its Best

The included M5 earth ground stud and 250-millimeter-long earth wire help reduce unwanted leakage currents between connected devices.

#### Comes Ready to Install and Use Right Out of the Box

Built-in mounting tabs and flanges let you install the PS610HGUK on a wide variety of surfaces, including IV poles, mobile carts, crash carts and mobile medical workstations. The durable all-metal housing is designed to last a long time in demanding work environments.

#### 2-Year Warranty and Environmentally Responsible Design

The PS610HGUK comes with a 2-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

### Highlights

- Meets BS-1363 specifications for use inside and outside patient-care vicinities
- Long 3m UK power cord allows you great flexibility in placing the power strip
- Replaceable 13A fuse shuts down all 6 UK outlets in case of overload
- Mounting tabs/flanges for installation on IV poles, mobile carts and crash carts
- Switchless design protects connected devices from dangerous accidental shutdowns

### Applications

- Medical-grade power distribution for IV poles, mobile carts, crash carts and mobile medical workstations inside and outside operating rooms and other patient-care vicinities

### Package Includes

- PS610HGUK UK BS-1363 Medical-Grade Power Strip with 6 UK Outlets, 3m Cord
- Owner's manual



## Specifications

OVERVIEW	
UPC Code	037332203250
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) British BS 1363A
Overload Protection	13A in plug fuse
Outlet Orientation	Single row of 6
Right-Angle Outlets	Yes
INPUT	
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
USER INTERFACE, ALERTS & CONTROLS	
Audible Alarm	NO ALARM
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.94 x 6.97 x 22.83
Shipping Dimensions (hwd / cm)	10.01 x 17.70 x 57.99
Shipping Weight (lbs.)	4.59
Shipping Weight (kg)	2.08
CERTIFICATIONS	
UL1363 (Power Tap)	BS 1363
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>