

7445 Kraftform adjustable torque screwdrivers with Rapidaptor quick-release chuck, 1/4 inch, 2,5 - 11,5 in. lbs.
Series 7400 Kraftform Torque Screwdrivers



EAN:	4013288102881	Size:	155x37x37 mm
Part number:	05074710001	Weight:	177 g
Article number:	7400 inch	Country of origin:	CZ
		Customs tariff number:	82041100



- Adjustable Kraftform torque screwdriver with Rapidaptor quick-release chuck
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached
- Numerical torque value indicator

Wera torque screwdriver. Dependable protection against electrostatic energy and associated damage. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_series_7400_kraftform_torque_screwdrivers_7400_inch.html

Wera - 7400 inch
05074710001 - 4013288102881

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Adjustable Torque Screwdrivers



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

Simple setting



Simple setting of the required torque by hand.

Easy-to-read



Easy-to-read scale value.

Attachable magnifying glass



Articles 7430, 7431 and 7432 all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

Measurement accuracy



Measurement accuracy is $\pm 6\%$ in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Unlimited torque








Unlimited torque for loosening seized screws.

Versatile



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Further versions in this product family:

							
	art. no.	inch	in. lbs.	in. lbs.	mm	inch	
	05074710001	7445	1/4	2.5-11.5	0.5	155	6
	05074711001	7446	1/4	11.0-29.0	1.0	155	6

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_series_7400_kraftform_torque_screwdrivers_7400_inch.html

Wera - 7400 inch

05074710001 - 4013288102881

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de