

From Off-The-Shelf to Market-Ready© New Age Enclosures is your Single Source Solution.


Let us quote modifiying our Stock Enclosures to meet your end-use.

visit newageenclosures.com/services or call 855-4NA-ENCL today.









NEW AGE ENCLESURES





DEVELOP THE FUTURE

NOTES: UNLESS OTHERWISE SPECIFIED

- 1. CORNERS DRAWN SHARP TO BE R.005 MAXIMUM.
- EXTERIOR SURFACE TEXTURE TO BE LIGHT EDM FINISH. EQUIVALENT TO MT-11010.
- 3. INTERIOR SURFACE TEXTURE TO BE: NONE.
- 4. ALL INSIDE RADII .010R. UNLESS OTHERWISE SPECIFIED.
- ALL EXTERNAL DIMENSIONS AFFECTED BY THE DRAFT APPLY AT THE LARGE END OF THE FEATURE, AND ALL INTERNAL FEATURES AFFECTED BY THE DRAFT APPLY AT THE SMALL END OF THE FEATURE UNLESS OTHERWISE SPECIFIED.
- 1 DEGREE DRAFT IN THE DIRECTION OF PULL IS PERMISSIBLE UNLESS OTHERWISED SPECIFIED.
- MATERIAL / COLOR: ABS PLASTIC IS STANDARD IN BLACK OR WHITE. CUSTOM MATERIALS AND COLORS ARE AVAILABLE UPON REQUEST FOR QUOTE. ALTERNATE RESINS HAVE DIFFERENT SHRINK RATES, AND WILL EFFECT DIMENSIONS.
- PCB SIZES ARE RECOMMENDATIONS ONLY. FINAL SIZES AND VERIFICATION OF ITS FIT ARE THE SOLE RESPONSIBILITY OF EACH CUSTOMER.
- 9. ASSEMBLY SCREWS FOR THE ENCLOSURE INCLUDED.
- 10. THIS DRAWING IS BASED ON A SOLID MODEL, AND IS FURTHER DEFINED BY THE SOLID MODEL FILE.
- 11. ALLOWABLE FLASH: 0.015 MAX.
- 12. ALL EJECTOR PIN MARKS TO BE WITHIN 0.015" OF FLUSH, PROTRUDING OR BELOW FLUSH.
- 13. TRIM GATE WITHIN 0.030" OF FLUSH.

R E V I S I O N								
REV.	DRAWN BY	ECO No	DESCRIPTION	DATE	APPROVED			
Α	R CRUZ	DR XXX	PRELIMINARY RELEASE	2016-Jul-07	D.C.			
В	R CRUZ		UPDATE NOTE 2, CASE SIZE, PRODUCT NAME, RECESS	2016-Jul-14	D.C.			
С	M BOYER		UPDATE DIMENSIONS	2016-Sep-08	D.C.			
D	R CRUZ		UPDATE NOTE 2, ENCLOSURE NAME, & PCB SHAPE	2016-Oct-06	D.C.			
Е	R CRUZ		ADD RIBS ON BASE, REVISE PCB SHAPE AND ADD NOTE	2016-Nov-30	D.C.			
1.0	M BOYER		RELEASED TO MFG PER CUSTOMER	2017-Feb-15				





	MANUFACTURE ANY ITEMS.						
ITEM	FILE NAME	DESCRIPTION	MATERIAL	COLOR	QTY.	DISCLOSED WITHOUT THE EXPRESS WRI' CONSENT OF ALL'TEC INTEGRATED MFG I POSSESSION OF THIS DOCUMENT DOES NOT CONSTITUTE A GRANT TO	
1	SCREW_HILO-NO4X375	#4 HiLo x .375" SCREW	ZINK PLATED	3/8" LONG	4	CONTROL THAT THIS DOCUMENT WILL NOT BE COPIED, REPRODUCED, OR	
2	301810_BASE	301810 BASE - STANDARD	ABS	BLACK or WHITE	1	MFG INC & SHALL REMAIN THE EXCLUSIVE PROPERTY OF ALLTEC INTEGRATED MFG	
3	301810_COVER	301810 COVER - STANDARD	ABS	BLACK or WHITE	1	NOTICE: THE INFORMATION AND DATA CONTAINED HEREIN IS CONSIDERED PROPRIETARY TO ALL TECHNOLOGICAL	
4	301810_PCB_062	301810 PCB - REFERENCE	.062" THICK	CUSTOMER SUPPLIED	1	DO NOT SCALE DRAWIN	
	DO NOT SCALE DRAWIN						

BILL OF MATERIALS

THIRD ANGLE PROJECTION	TOLERANCES: UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN U.S. INCHES. X.XX = .015					
DO NOT SCALE DRAWING	NEW	NEW AGE ENCLOSURES				
NOTICE: THE INFORMATION AND DATA CONTAINED HEREIN IS CONSIDERED	Customer's Part No: 301810					
PROPRIETARY TO ALLTEC INTEGRATED MFG INC & SHALL REMAIN THE EXCLUSIVE	APPROVAL	BY DATE				
PROPERTY OF ALLTEC INTEGRATED MFG INC THE HOLDER WILL ASSUME CUSTODY AND	CHECK					
CONTROL THAT THIS DOCUMENT WILL NOT BE COPIED, REPRODUCED, OR	ENG.					
DISCLOSED WITHOUT THE EXPRESS WRITTEN CONSENT OF ALLTEC INTEGRATED MFG INC	SCALE	AS NOTED				
POSSESSION OF THIS DOCUMENT DOES NOT CONSTITUTE A GRANT TO MANUFACTURE ANY ITEMS. © 2016	DRAWN BY R CRUZ	2016-Jul-07				


NEW AGE ENCLESURES


4330 Santa Fe Road ph. (805) 595-1310 San Luis Obispo, CA. 93401 fax (805) 595-1024 www.newageenclosures.com


STANDARD - MULTI-PORT BAR SXX-301810-XXX


SXX - 301810 - XXX

SIZE DRAWING NAME
A 301810_R1_0 SHEET REV.DOC
1 OF 6 1.0










301810 - 2nd OPERATION DETAILS
NEW AGE ENCLOSURES DELIVERS YOUR ENCLOSURE MARKET-READY WITH IN-HOUSE CNC MACHINING, PAD PRINTING, ASSEMBLY, AND FULFILLEMENT. ALL SURFACES AND AREAS ARE AVAILABLE FOR CNC ALTERATION BY NEW AGE ENCLOSURES CALL (805) 595-1310 FOR PRICING AND SCHEDULE. THE INSIDE RADIUS OF ANY MACHINED FEATURES SHOULD BE NO SMALLER THAN .031"



SXX-301810-XXX COVER - ABS, BLACK						TOLERANCES: UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN U.S. INCHES. X.XX = .015 X.XXXX = .001		NEW AGE ENCLESURES					
STEP NO	DESCRIPTION		CUTTER	FIXTURE	ORIENTATION	PROGRAM	X.XXX = .010 X.X° = 1° NEW AGE ENCLOSURES				bispo, CA. 9340		
1-C-C1	-		T2 = .062" EM	-			Customer's Part No: 301810		ph. (805) 595-1310 fax (805) 595-1024 www.newageenclosures.com				
2-C-C2	-		T2 = .062" EM	-			APPROVAL CHECK	BY DATE	C 7	ANDARD - MULTI		BAR	
SXX-301810-XXX COVER - ABS, BLACK									יכן	SXX-301810		DAN	
STEP NO	DESCRIPTION	INK COLOF		CLICHE DESCRIPTION		CLICHE No.	SCALE DRAWN BY	AS NOTED	SIZE	DRAWING NAME	SHEET	REV.DOC	
3-C-P1	PAD PRINT					CLXXXX R1	R CRUZ	2016-Jul-07		301810_R1_0	6 OF 6		