

Ordering a market-ready enclosure® is made fast and affordable with our complete in-house capabilities. New Age provides machined openings to fit your PCB, pad printing for your graphics, custom enclosures, custom colors, final assembly, testing and fulfillment services to save you additional time and money.

Ask your representative for a free quote today 805-595-1310.

## Fast and Affordable Customization

ISO quality off-the-shelf to market-readv<sup>©</sup>

CNC Modifications
Pad Printing
Colored Resins
EMI/RF Shielding
Custom Enclosure
Assembly & Testing


## NEW AGE ENCLESURES

www.NewAgeEnclosures.com 4330 Santa Fe Road • San Luis Obispo, CA 93401 • T 805.595.1310 • F 805.595.1024

P260906(x) CONFIGURATIONS				
	-S	-U		
P260906 COVER	1			
P260906 COVER w/ USB		1		
P260906 BASE	1			
P260906 BASE w/ USB		1		


4	M2 SCREW x 4mm - REFERENCE	CUSTOMER SUPPLIED	CUSTOMER SUPPLIED	4
3	260906 COVER - STANDARD	ABS	BLACK or WHITE	1
2	260906 BASE - STANDARD	ABS	BLACK or WHITE	1
1	260906 PCB - REFERENCE	CUSTOMER SUPPLIED	.062" THICK	1
ITEM	DESCRIPTION	MATERIAL	COLOR	QTY.


		МΔТ		



### NOTES: UNLESS OTHERWISE SPECIFIED

- 1. CORNERS DRAWN SHARP TO BE R.005 MAXIMUM.
- 2. EXTERIOR SURFACE TEXTURE TO BE LIGHT EDM FINISH. EQUIVALENT TO MT-11020.
- 3. INTERIOR SURFACE TEXTURE: NONE
- 4. ALL INSIDE RADII .010R. UNLESS OTHERWISE SPECIFIED.
- 5. ALL EXTERNAL DIMENSIONS AFFECTED BY THE DRAFT APPLY AT THE LARGE END OF THE FEATURE, AND ALL INTERNAL FEATURES AFFECTED BY THE DRAFT APPLY AT THE SMALL END OF THE FEATURE UNLESS OTHERWISE SPECTFIED.
- 1 DEGREE DRAFT IN THE DIRECTION OF PULL IS PERMISSIBLE UNLESS OTHERWISED SPECIFIED.
- THIS ENCLOSURE IS A PRESS FIT ASSEMBLY. FOR PERMANENT CLOSURE: A DROP OF ADHESIVE OR ULTRASONIC WELDING IS REQUIRED.
- 8. MOUNTING SCREWS FOR THE PCB ARE CUSTOMER SUPPLIED.
- MATERIAL / COLOR: ABS PLASTIC IS STANDARD IN BLACK OR WHITE. CUSTOM MATERIALS AND COLORS ARE AVAILABLE UPON REQUEST FOR QUOTE.
- 10. PCB SIZES ARE RECOMMENDATIONS ONLY. FINAL SIZES AND VERIFICATION OF ITS FIT ARE THE SOLE RESPONSIBILITY OF EACH CUSTOMER.
- 11. STANDARD OR CUSTOM LABEL RECESSES ARE AVAILABLE FOR QUOTE.








SCALE 1.500

THIRD ANGLE PROJECTION TOLERANCES: UNLESS OTHERWISE SPECIFIED NEW ACTION

DO NOT SCALE DRAWING	X.XX = .0 X.XXX = .	NSIONS ARE IN U.S. INCHES.  15 X.XXXX = .001  010 X.X° = 1°  AGE ENCLOSURES	1.00	NCLESU 4330 Santa Fe Road ph. (805) 595-1310 San Luis Obis fax (6		
NOTICE: THE INFORMATION AND DATA CONTAINED HEREIN IS CONSIDERED	Custome	er's Part No: 260906		www.newageenclosure		
PROPRIETARY TO ALL'TEC INTEGRATED MFG INC & SHALL REMAIN THE EXCLUSIVE	APPROVAL	BY DATE		TANDADD MINIT	DEMC	\T.F.
PROPERTY OF ALLTEC INTEGRATED MFG INC THE HOLDER WILL ASSUME CUSTODY AND	CHECK		) >	TANDARD - MINI	REMU	)   E
CONTROL THAT THIS DOCUMENT WILL NOT BE COPIED, REPRODUCED, OR	ENG.		lι	PXX-260906X AS	CEMBI	V
DISCLOSED WITHOUT THE EXPRESS WRITTEN CONSENT OF ALLTEC INTEGRATED MFG INC	SCALE	AS NOTED	'	7X7-200300X A3	SLMDL	- '
POSSESSION OF THIS DOCUMENT DOES NOT CONSTITUTE A GRANT TO MANUFACTURE ANY ITEMS.	DRAWN BY		SIZE	DRAWING NAME	SHEET	REV.DOC
© 2014	M BOYER	08-Apr-08	А	260906_R5_2	1 OF 6	5.2








P260906 PCB - CUSTOMER SUPPLIED

PCB SIZES ARE RECOMMENDATIONS ONLY. FINAL SIZES AND VERIFICATION OF ITS FIT ARE THE SOLE RESPONSIBILITY OF THE OEM.



TOLERANCES: UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN U.S. INCHES.  X.XX = .015  X.XXXX = .001  X.XXX = .010  X.X° = 1°	NEW AG	E Sures
NEW AGE ENCLOSURES	4330 Santa Fe Road ph. (805) 595-1310	
Customer's Part No: 260906		geenclosures.com
APPROVAL BY DATE	CTANDADD	MINIT DEMOTE

STANDARD - MINI REMOTE ENG. PXX-260906X ASSEMBLY AS NOTED


SCALE FEV.DOC 5.2 SIZE DRAWING NAME DRAWN BY M BOYER A 260906\_R5\_2 5 OF 6 08-Apr-08

2nd OPERATION DETAILS


NEW AGE ENCLOSURES DELIVERS YOUR ENCLOSURE MARKET-READY WITH IN-HOUSE CNC MACHINING, PAD PRINTING, ASSEMBLY, AND FULFILLEMENT.


ALL SURFACES AND AREAS ARE AVAILABLE FOR CNC ALTERATION BY NEW AGE ENCLOSURES CALL (805) 595-1310 FOR PRICING AND SCHEDULE.


THE INSIDE RADIUS OF ANY MACHINED FEATURES SHOULD BE NO SMALLER THAN .031"




















PXX-260906X-XXX COVER - ABS, BLACK						
STEP NO	DESCRIPTION	CUTTER	FIXTURE	ORIENTATION	PROGRAM	
1	-	T2 = .062" EM	106	-	-	
2	-	T2 = .062" EM	106	-	-	

PXX-260906X-XXX BASE - ABS, BLACK						
STEP NO	DESCRIPTION	CUTTER	FIXTURE	ORIENTATION	PROGRAM	
4	-	T2 = .062" EM	106	-	-	
5	-	T2 = .062" EM	106	-	-	

١	TOLERANCES: UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN U.S. INCHES.
•	X.XX = .015
	NEW AGE ENCLOSURES

Customer's Part No: 260906

-	APPROVAL	BY	DATE	ı
╡	CHECK			
	ENG.			
	SCALE		AS NOTED	
4	DRAWN BY			S
	M BOYER	08-A	Apr-08	

# NEW AGE ENCLSSURES 4330 Santa Fe Road ph. (805) 595-1310 San Luis Obispo, CA. 93401 fax (805) 595-1024

www.newageenclosures.com

STANDARD - MINI REMOTE PXX-260906X ASSEMBLY

SIZE DRAWING NAME REV.DOC A 260906\_R5\_2 6 OF 6 5.2