

Active High-Speed HDMI Cable with Built-In Signal Booster, 1920 x 1080 (1080p) @ 60 Hz (M/M), Black, 100 ft.

MODEL NUMBER: P568-100-ACT



High-speed long-range premium cable connects two HDMI devices up to 100 ft. apart. Built-in signal booster avoids the expense and effort of connecting a repeater between two separate HDMI cables.

Description

The P568-100-ACT Active High-Speed HDMI Cable (M/M) connects a computer, cable box or Blu-ray™ source to a high-definition monitor, projector or television up to 100 feet away. Its built-in signal booster allows a clean audio/video transmission without the effort and expense of adding an external repeater to your HDMI cable run. Plus, a built-in equalization control lets you manually adjust the display image to your liking.

The P568-100-ACT is recommended for digital signage, boardroom and classroom presentations, point-of-sale displays, businesses and other applications that display HD video and multi-channel audio. It supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz. When used with an Apple® digital A/V adapter, it supports iPad2® video mirroring for playing games, watching videos or displaying presentations. Backward compatible with previous HDMI generations, the P568-100-ACT is compliant with HDCP v1.3 standards.

The 100-foot molded 28 AWG cable features foil and braid shielding to deliver top-of-the-line signal quality and protection from crosstalk and EMI/RFI interference. Corrosion-resistant gold-plated connectors and contacts provide maximum conductivity and minimize data loss. Integral strain relief with ridges on each end gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. A flexible PVC jacket makes the cable easy to install in tight spaces.

Features

Connects HDMI Source to High-Definition TV, Projector or Monitor

- Recommended for digital signage, boardroom and classroom presentations, point-of-sale displays,

Highlights

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Signal booster allows clean signal transmission up to 100 ft.
- Built-in equalization control allows manual image adjustment
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated connectors for optimal signal transfer

Package Includes

- P568-100-ACT Active High-Speed HDMI Cable with Built-In Signal Booster (M/M), Black, 100 ft.
- HDMI power adapter cable



businesses and other applications that display HD video and multi-channel audio

Built-In Signal Booster for Long-Range Cable Needs

- Allows a clear A/V transmission up to 100 ft.
- Eliminates expense and effort of adding external repeater to cable run
- Equalization control allows manual adjustment of display image

High Performance and Wide Compatibility

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Backward compatible with previous HDMI generations
- Complies with HDCP v1.3 standards

Superior Quality Ensures a Flawless Signal

- Corrosion-resistant gold-plated black connectors for optimal signal transfer
- Fully molded 28 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332200686
Technology	HDMI
INPUT	
Cable Length (ft.)	100
Cable Length (m)	30.5
PHYSICAL	
Color	Black
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>