

## MCX Plug to BNC Female (Jack) Adapter, 1.35 VSWR

MCX plug to BNC female adapter part number SM3665 from Fairview Microwave is in-stock and ships same day. This Fairview MCX to BNC adapter has a plug to female gender configuration. SM3665 MCX plug to BNC female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.35:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 2	2 to 6				GHz
VSWR, Max	1.2:1	1.35:1				

### Mechanical Specifications

<b>Size</b>	
Length	1.246 in [31.7 mm]
Width	0.45 in [11.43 mm]
Weight	0.0302 lbs [13.7 g]

Description	Connector 1	Connector 2
Type	MCX Plug	BNC Female
Polarity	Standard	Standard

### Material Specifications

Description	Connector 1	Connector 2
Type	MCX Plug	BNC Female
Contact Material	Beryllium Copper	Brass
Contact Plating	Gold	Gold
Contact Plating Spec.	MIL-G-45204	MIL-G-45204
Insulation Material	PTFE	PTFE
Body Material	Brass	Brass
Body Plating	Nickel	Nickel



### Configuration:

- MCX Plug Connector 1
- BNC Female Connector 2
- 50 Ohm
- Straight Body Geometry

### Features:

- VSWR of 1.35:1 max up to 6 GHz
- Contact plating according to MIL-G-45204

### Applications:

- Enables Between Series Connections
- General Purpose Test


Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**Typical Performance Data**



MCX Plug to BNC Female (Jack) Adapter, 1.35 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [MCX Plug to BNC Female \(Jack\) Adapter, 1.35 VSWR SM3665](#)

URL: <https://www.fairviewmicrowave.com/mcx-plug-bnc-female-adapter-sm3665-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

