



## Main

Range of Product	9080G
Product Type	Terminal block
Localisation on Device	Standard
Color	Natural
Quantity	Set of 50

## Complementary

Voltage Rating	600 V AC/DC
Current Rating	30 A UL 30 A CSA
Wire Size	AWG 22...AWG 10 copper
Mounting Type	9080GH track 35 mm DIN rail
Certifications	CE CSA file 62144 class 6228 01 UL recognized E60616 CCN XCFR2
Protection Type	Fingersafe DIN 57470
Electrical Connection	Zinc plated steel box lugs
Material	Nylon block Tin plated brass busbar
Ambient Air Temperature for Operation	-40...257 °F (-40...125 °C)
Electrical Connection Tightening Torque	Lug zinc plated steel 7...8 lbf.in (0.79...0.90 N.m) : AWG 22...AWG 10 copper)
Height	1.82 in (46.23 mm)
Width	1.72 in (43.69 mm)
Depth	0.235 in (5.97 mm)
Density	51 per foot
Compatible End Barrier	GM6B

## Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	785901743927
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.20 in (0.508 cm)
Package 1 Width	1.70 in (4.318 cm)
Package 1 Length	1.70 in (4.318 cm)
Package 1 Weight	0.28 oz (8.0 g)

Unit Type of Package 2	CAR
Number of Units in Package 2	500
Package 2 Height	6.00 in (15.24 cm)
Package 2 Width	12.50 in (31.75 cm)
Package 2 Length	16.00 in (40.64 cm)
Package 2 Weight	9.47 lb(US) (4.294 kg)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------