



Main

Range of Product	Harmony XAC
Product or Component Type	Head for emergency switching off push-button
Sale per indivisible quantity	1

Complementary

Product Compatibility	XACA..
Mounting Location	Front of enclosure
Overvoltage category	Class II IEC 61140
Operator profile	Red mushroom Ø 30 mm
Product Weight	0.09 lb(US) (0.04 kg)
Marking	Unmarked

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 UL 508 EN/IEC 60204-32 EN/IEC 60947-5-5 EN 50102
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
IK Degree of Protection	IK08

Ordering and shipping details

Category	22460-PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
GTIN	3389110591750
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.73 in (4.4 cm)
Package 1 Width	3.66 in (9.3 cm)
Package 1 Length	1.73 in (4.4 cm)
Package 1 Weight	1.41 oz (40 g)

Unit Type of Package 2	S01
Number of Units in Package 2	40
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	3.99 lb(US) (1.81 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	1280
Package 3 Height	30.31 in (77 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	146.43 lb(US) (66.42 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------