



Main

Range	PowerLogic
Product or Component Type	Current transformer
Accessory / separate part category	Measurement accessory

Complementary

Range compatibility	PowerLogic (PowerLogic PM5000) power meter PowerLogic (PowerLogic PM3000) power meter Acti 9 (Acti9 iEM3000) energy meter EasyLogic (EasyLogic PM2100) power meter EasyLogic (EasyLogic PM2200) power meter
Current transformer type	Split core
Primary operational current	800 A
Secondary current	5 A
Network type	AC
Network Frequency	50 Hz 60 Hz
Current transformer ratio	800/5
Electrical connection	8 ft (2.44 m) AWG 16 flying lead
Insulation	Basic insulation 600 V AC Reinforced insulation 300 V AC
Measurement accuracy	1 %
Mounting Location	Indoor use only
Width	Internal 2.46 in (62.48 mm) Total 5.83 in (148.08 mm)
Depth	1.12 in (28.45 mm)
Height	Internal 2.9 in (73.66 mm) Total 5.36 in (136.14 mm)
Product Weight	38.69 oz (1097 g)

Environment

Relative humidity	0...95 % non condensing
Installation category	III
Pollution degree	2
Ambient air temperature for operation	5...140 °F (-15...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Operating altitude	<= 6561.68 ft (2000 m)
Product certifications	UL

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	09661-POWERLOGIC BASIC CTS
Discount Schedule	PL1
GTIN	3606489703585
Returnability	Yes

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.43 in (8.7 cm)
Package 1 Width	10.16 in (25.8 cm)
Package 1 Length	8.43 in (21.4 cm)
Package 1 Weight	3.20 lb(US) (1.45 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.