



## Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Terminal extension
Accessory / separate part category	Extension accessories

## Complementary

Range compatibility	LC1G
Product Compatibility	LC1G630...800 LC1G620
Connector Type	Large
Height	6.69 in (170 mm)
Width	3.94 in (100 mm)
Depth	2.24 in (57 mm)
Net Weight	6.15 lb(US) (2.79 kg)
Quantity per Set	Set of 3

## Environment

Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048
Pollution degree	3 IEC 60947-1

## Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	3606481015952
Nbr. of units in pkg.	1
Package weight(Lbs)	5.73 lb(US) (2.598 kg)
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 in (6.5 cm)
Package 1 width	4.72 in (12.0 cm)
Package 1 Length	7.87 in (20.0 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	3
Package 2 Weight	18.25 lb(US) (8.277 kg)
Package 2 Height	5.91 in (15.0 cm)
Package 2 width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product