

Product data sheet

Specifications



APC Replacement Battery Cartridge, Valve regulated lead-acid battery, 7Ah, 12VDC, 2-year warranty

RBC2

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Replacement battery cartridge
Number Of Cables	1
Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Voltage	12 V
Rbc Quantity	1

Physical

Color	Black
Height	3.70 in (9.4 cm)
Width	2.52 in (6.4 cm)
Depth	5.94 in (15.1 cm)
Net Weight	5.51 lb(US) (2.5 kg)
Mounting Mode	Not rack-mountable
Usb Compatible	No

Output

Battery Capacity	7.0 Ah
------------------	--------

Environmental

Ambient Air Temperature For Operation	32...104 °F (0...40 °C)
Operating Altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	5...113 °F (-15...45 °C)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage Altitude	0...50000 ft (0.00...15240.00 m)
------------------	----------------------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Ordering and shipping details

Gtin	731304003243
------	--------------

Country Of Origin	VN
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	3.50 in (8.9 cm)
------------------	------------------

Package 1 Width	6.89 in (17.5 cm)
-----------------	-------------------

Package 1 Length	8.39 in (21.3 cm)
------------------	-------------------

Package 1 Weight	6.11 lb(US) (2.77 kg)
------------------	-----------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 RoHS Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov