

2303 E-2RS1TN9

Self-aligning ball bearing with seals on both sides



Self-aligning ball bearings, with seals on both sides, have two rows of balls, a common sphered raceway in the outer ring and two deep uninterrupted raceway grooves in the inner ring. They are insensitive to angular misalignment of the shaft relative to the housing. The integral sealing can significantly prolong bearing service life because it keeps lubricant in the bearings and contaminants out.

- Accommodate static and dynamic misalignment
- Excellent high-speed performance
- Excellent light load performance
- Low friction
- Integral sealing results in reduced maintenance requirements and prolonged bearing service life

Overview

Dimensions

Bore diameter	0.669 in
Outside diameter	1.85 in
Width	0.748 in


Properties

Bore type	Cylindrical
Cage	Non-metallic
Coating	Without
Locating feature, bearing outer ring	None
Lubricant	Grease
Material, bearing	Bearing steel
Radial internal clearance	CN
Relubrication feature	Without
Retaining feature, inner ring	None
Sealing	Seal on both sides
Sealing type	Contact
Tolerance class	Normal

Technical Specification


Bore type

Cylindrical



Dimensions

d	0.669 in	Bore diameter
D	1.85 in	Outside diameter
B	0.748 in	Width
d ₂	≈ 1.004 in	Recess diameter inner ring
D ₂	≈ 1.623 in	Recess diameter outer ring
r _{1,2}	min. 0.039 in	Chamfer dimension



Abutment dimensions

d _a	min. 0.866 in	Abutment diameter shaft
d _a	max. 1.004 in	Abutment diameter shaft
D _a	max. 1.63 in	Abutment diameter housing
r _a	max. 0.039 in	Fillet radius

Calculation data

Basic dynamic load rating	C	2 855 lbf
Basic static load rating	C ₀	764 lbf
Fatigue load limit	P _u	40 lbf
Limiting speed		10 000 r/min

Permissible angular misalignment	α	1.5 °
Calculation factor	k_r	0.05
Limiting value	e	0.3
Calculation factor	Y_0	2.2
Calculation factor	Y_1	2.1
Calculation factor	Y_2	3.3

Mass

Mass bearing	0.353 lb
--------------	----------

Terms and conditions

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app. Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service. Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.