

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0193240003**
Status: **Active**
Overview: Metric Ring Terminals
Description: Avikrimp Metric Ring Terminal for Stud Size 5-6 (M3-3.5), Insulated Barrel

Documents:

3D Model	3D Model (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E32244
----	--------

General

Product Family	Ring and Spade Terminals
Series	<u>19324</u>
Crimp Quality Equipment	Yes
Overview	<u>Metric Ring Terminals</u>
Product Name	Avikrimp
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	887191290034

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.747/g
Packaging Type	Bag
Stud Size	M3.5
Wire Size AWG	N/A
Wire Size mm ²	0.50-1.00

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Engineering Number	AA1-832-M3,5
--------------------	--------------

Reference - Drawing Numbers

Sales Drawing	SD-19324-001-001
---------------	------------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19324 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade	<u>640010100</u>
--------------	------------------

Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)
Crimp Head for the AT-200 Pneumatic Hand Tool

<u>640050100</u>

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION