

Eaton FWP-50A22F

Catalog Number: FWP-50A22F

Eaton Bussmann series FWP high speed fuse, 700 Vac, 700 Vdc (UL), 50A, 200 kAIC at 300 Vdc, 50 kAIC at 300 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

General specifications

Product Name	Catalog Number
Eaton Bussmann series high speed cylindrical fuse	FWP-50A22F
	UPC
	051712796569
EAN	Product Length/Depth
5027590500869	58 mm
Product Height	Product Width
23 mm	23 mm
Product Weight	Warranty
62.6 g	Not Applicable
Compliances	Certifications
CE Marked RoHS Compliant	CSA Certified UL Recognized



Product specifications

Interrupt rating

200 kAIC

Release characteristic

Other

Amperage Rating

50 A

Frequency rating - max

62 Hz

Fuse type

FWP-A22F

Accessories

JM70100 Fuse base

Minimum melting

135 I2t (A2 sec)

Fuse size

14 x 51 mm

Voltage rating

700 V

Fuse indicator

Other

Construction size

22 mm x 58 mm

Clearing (I2T)

2200

Color

White

Connection

Ferrule end x ferrule end

Quantity

10

Material

Ceramic

Utilization category

aR (accompanied semiconductor protection)

Watt losses

Resources

Catalogs

IEC high speed fuse links

Bussmann series complete full line catalog no. 1007

Compliance information

UKCA FWC-*A10F,FWH-*A14F,FWP-*A14F,FWP-*A14FI etc

CE FWC-*A10F,FWH-*A14F,FWP-*A14F,FWP-*A14FI etc

Specifications and datasheets

Eaton Specification Sheet - FWP-50A22F

12.5 W

Type

High speed fuse

Fuse shape

Cylindrical

Used with

Finger safe holders/blocks and striker

Breaking capacity

200 kA

Frequency rating - min

45 Hz

Class

Class aR

Pre arc (I2T)

155

Application

Semiconductor, DC Common bus, DC drives, Power converters/rectifiers

Voltage type

AC/DC

Packaging type

Standard



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)