

# AD BS88 Centre bolted tags fuse links



## Product description

Eaton's Bussmann® series AD British Standard fuse links are specifically designed for the protection of general industrial applications e.g. power distribution, cable protection, motor protection.

## Standard features

- Good peak let-through current limitation
- 1:1:6 Selective coordination ratio between 'minor' and 'major' fuse
- gG characteristics for cable protection and general purpose applications
- Power loss values within the limits of IEC 60269-2

## Catalogue symbol

AD(Amps)

## Technical data

Rated voltage:

- 550 V a.c. / 250 V d.c. (2 to 20 A)
- 500 V a.c. / 250 V d.c. (25 to 32 A)

Rated current: 2 to 32 A

Breaking range and utilisation category: gG

Breaking capacity: 80 kA a.c / 40 kA d.c.

## Standards/Approvals

- BS88
- IEC 60269
- Suitable for use in RoHS compliant applications


## Packaging

MOQ 20

Table 1. Technical data


Catalogue number	Rated voltage	Rated current (Amps)	Breaking capacity	Energy integrals I <sup>2</sup> t (A <sup>2</sup> S)			Watts loss (W)	Product class	Weight (grams)
				Pre-arcing	Total at 415 V a.c.	Total at 550 V a.c.			
AD2	550 V a.c./ 250 V d.c.	2	80 kA at 550 V a.c. / 40 kA at 250 V d.c.	1.2	3.1	3.8	1.2	gG	60
AD4		4		11	31	38	1.4		
AD6		6		32	90	125	1.8		
AD10		10		20	60	80	2.4		
AD16		16		85	240	320	2.9		
AD20		20		220	580	770	3.1		
AD25	500 V a.c./ 250 V d.c.	25	80 kA at 500 V a.c. / 40 kA at 250 V d.c.	500	1400	1850	3.2	gG	60
AD32		32		1000	2760	3700	3.5		

## Dimensions - mm



Catalogue numbers	A	B	C	D	E	F	G	H	K
AD2-32	128.5	111	55	21	1.4	14.2	11.8	8.7	11.2

Time-current characteristic curve



Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, and Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton Internet pages and Eaton order confirmations.

Eaton  
EMEA Headquarters  
Route de la Longeraie 7  
1110 Morges, Switzerland

Eaton Electrical Products Limited  
Melton Road  
Burton-on-the-Wolds  
Leicestershire, LE12 5TH  
United Kingdom

© 2017 Eaton  
All Rights Reserved  
PDF Only  
Publication No. 4111  
October 2017