

LED Wallpack Retrofits

60WP/LED/850/LS EX39 G3 BB 3/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000
Tier	CorePro
Light technical	
Color Code	850 [CCT of 5000K]
Initial lumen (Nom)	9000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	150.00 lm/W
Color Consistency	ANSI 5000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	60 W


Lamp Current (Nom)	666 mA
Wattage Equivalent	250(175-250) W
Starting Time (Nom)	1 s
Warm Up Time to 60% Light (Nom)	1 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Ambient (Max)	113 °F
T-Ambient (Min)	-4 °F
T-Case Maximum (Nom)	149 °F
Controls and dimming	
Dimmable	Preset Dimming
Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Plastic

LED Wallpack Retrofits

Bulb Shape	Wall Pack
Product data	
Order product name	60WP/LED/850/LS EX39 G3 BB 3/1
EAN/UPC - Product	046677564292
Order code	564294

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	929003000404
Net Weight (Piece)	2.064 lb


Dimensional drawing




60WP/LED/850/LS EX39 G3 BB 3/1

Product	D	C
60WP/LED/850/LS EX39 G3 BB 3/1	3-5/8 in	10-5/8 in


Photometric data



LEDTForce LS EX39 60W WallPack EX39 850-POC



LEDTForce LS EX39 40W WallPack EX39-LDD




General Uniform Lighting

LEDTForce LS EX39 60W WallPack EX39 850-GUL

LED Wallpack Retrofits

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

