



LED PAR30 S/L

9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General information		Warm Up Time to 60% Light (Nom)	
Base	E26 [Single Contact Medium Screw]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.9
Nominal Lifetime (Nom)	25000 h	Voltage (Nom)	120 V
Switching Cycle	50000	Temperature	
		T-Case Maximum (Nom)	176 °F
		Controls and dimming	
		Dimmable	Yes
		Mechanical and housing	
		Bulb Finish	Clear
		Bulb Material	Plastic
		Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
		Approval and application	
		Suitable For Accent Lighting	Yes
		Energy Consumption kWh/1000 h	- kWh
		Energy Certifications	Energy Star
		Product data	
		Order product name	9.4PAR30S/COR/930/F25/DIM/120V T20
			6/1FB
		EAN/UPC - Product	046677546984
Light technical			
Color Code	930 [CCT of 3000K]		
Beam Angle (Nom)	25 °		
Initial lumen (Nom)	850 lm		
Luminous Intensity (Nom)	2910 cd		
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	90.00 lm/W		
Color Consistency	<4		
Color Rendering Index (Nom)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and electrical			
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	9.4 W		
Lamp Current (Nom)	90 mA		
Wattage Equivalent	75 W		
Starting Time (Nom)	0.5 s		

LED PAR30 S/L

Order code	546985
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002045604

Net Weight (Piece)	0.295 lb
--------------------	----------


Dimensional drawing




9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB

Product	D	C
9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	3-13/16 in	3-3/4 in


Photometric data



LEDspots 9,4W PAR30S E26 930 25D



LEDspots 9,4W PAR30S E26 930 25D



© 2022 Philips Lighting B.V. Page 11

LEDspots 9,4W PAR30S E26 930 25D

LED PAR30 S/L

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

