



# LED AR111

## 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

With an elegant new design, Philips MasterClass LED AR111 creates a brilliant visual effect. With excellent rendering of 90+ CRI and R9>50, colors stay vibrant and natural, enhancing the appeal of everything on display.

### Product data

General information	
Base	G53 [ G53]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	40000 h
Switching Cycle	50000
Light technical	
Color Code	930 [ CCT of 3000K]
Beam Angle (Nom)	8 °
Initial lumen (Nom)	680 lm
Luminous Intensity (Nom)	8000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	56.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	- Hz
Power (Rated) (Nom)	12 W
Lamp Current (Nom)	1300 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s


Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	AR111
Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
Product data	
Order product name	12AR111/LED/930/S8/DIM/EC 12V 6/1FB
EAN/UPC - Product	046677552404
Order code	552406

LED AR111

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002238504

Net Weight (Piece)	0.353 lb
--------------------	----------



Dimensional drawing



12AR111/LED/930/S8/DIM/EC 12V 6/1FB

Product	D	C
12AR111/LED/930/S8/DIM/EC 12V 6/1FB	4-3/8 in	2-1/2 in


Photometric data



State of Parameters 01 Beam Lighting 01 Page 10

LEDspots 50W G53 AR111 930


LEDspots 50W G53 AR111 930 8D




LEDspots 50W G53 AR111 930 8D

LED AR111

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram

