



LED PAR38

10PAR38/LED/950/F25/DIM/GULW/T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General information		Warm Up Time to 60% Light (Nom)	
Base	E26 [Single Contact Medium Screw]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.9
Nominal Lifetime (Nom)	25000 h	Voltage (Nom)	120 V
Switching Cycle	50000	Temperature	
Light technical		T-Case Maximum (Nom)	158 °F
Color Code	950 [CCT of 5000K]	Controls and dimming	
Beam Angle (Nom)	25 °	Dimmable	Only with specific dimmers
Initial lumen (Nom)	900 lm	Mechanical and housing	
Luminous Intensity (Nom)	4100 cd	Bulb Finish	Clear
Color Designation	Daylight	Bulb Material	Glass
Correlated Color Temperature (Nom)	5000 K	Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Approval and application	
Color Consistency	<4	Suitable For Accent Lighting	Yes
Color Rendering Index (Nom)	90	Energy Certifications	Energy Star
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product data	
Operating and electrical		Order product name	10PAR38/LED/950/F25/DIM/GULW/T20 6/1FB
Input Frequency	50 to 60 Hz	EAN/UPC - Product	046677567880
Power (Rated) (Nom)	10 W	Order code	567883
Lamp Current (Nom)	97 mA		
Wattage Equivalent	90 W		
Starting Time (Nom)	0.5 s		

LED PAR38

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929003028904

Net Weight (Piece)	0.849 lb
--------------------	----------



Dimensional drawing



10PAR38/LED/950/F25/DIM/GULW/T20 6/1FB


Product	D	C
10PAR38/LED/950/F25/DIM/GULW/T20 6/1FB	4-13/16 in	5-1/8 in

Photometric data



LEDspots N DIM 10W PAR38 E26 950 25D-POC


LEDspots N DIM 10W PAR38 E26 950 25D 1-ADL



LEDspots N DIM 10W PAR38 E26 950 25D-LDD

LED PAR38

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram

