

LGFP 2/1



General purpose food grade grease

A clean, non-toxic bearing grease, which is based on medical white oil using an aluminium complex soap

- High resistance to water
- Excellent grease life
- Excellent corrosion resistance
- An essentially neutral pH value
- NSF H1 registered and Halal and Kosher certified

Overview

Performance

Copper corrosion (max.) DIN 51811 /ASTM D4048, 24 hrs at 100°C	1 max.at 120°C
Corrosion protection, Emcor, ISO 11007 modified, 0.5% NaCl	0-0
Corrosion protection, Emcor, ISO 11007 modified, Water washout	0-0
Corrosion protection, Emcor, ISO 11007, Distilled water	0-0
Dropping point (min) ISO 2176	482 °F
EP performance - 4 ball - Wear scar (max.) DIN 51350/5, 1400N	0.039 in
EP performance - 4 ball - Weld load (min.) DIN 51350/4	247 lbf
Low temperature torque, Start/Running, mNm	137/51 at -30°C
Lubrication ability, R2F test B at 120°C	Pass
Mechanical stability - Roll stability, ASTM D1831 (max.) 50 hrs at 80°C, 10-1mm	+50
Mechanical stability, V2F test, 144 hrs	-
Oil separation DIN 51817, 40°C, %	1-5
Penetration DIN ISO 2137, Prolonged (max.), 100 000 strokes, 10-1mm	+60
Penetration DIN ISO 2137, Worked, 60 strokes (10-1mm)	265-295
Product weight	2.205 lb
Rolling bearing grease life (max.) ROF test, L50 life, 10000 r/min, hrs at °C	1000 at 110°C

Speed (max.) n x dm (x 1000)	300
Water resistance (max.) DIN 51807/1, 3 hrs at 90 °C	1

Properties

Base oil type	White mineral oil
Certifications	NSF H1;Halal;Kosher
Colour	Transparent
DIN 51825 code	K2G-20
NLGI consistency class	2
NSF Registration no.	128004
Operating temperature range	-20 to +110 °C
Recommended applications	Conveyor bearings;Wrapping machines;Bottling machines
Thickener	Aluminium complex

Terms and conditions

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app. Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service. Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.