


## DIFFERENTIAL PRESSURE TRANSMITTER

NEMA 4X Enclosure, 0.25% Full-Scale Accuracy

**CALIBRATION SERVICES AVAILABLE** 







Positive, negative and differential pressures can be measured within a full span accuracy of  $\pm 0.25$  with the Series 616W Differential Pressure Transmitter. Units are enclosed in a polycarbonate case, rated NEMA 4X (IP66) and operate by sensing the pressure of air and compatible gases then sending a standard 4-20 mA output signal. Design enables operation in 2-wire current loops. A wide range of models are available factory calibrated to specific ranges. The span and zero controls are for use when checking calibration. They are not intended for re-ranging to a significantly different span. The LCD display allows local indication of pressure.

## BENEFITS/FEATURES

- NEMA 4X rated enclosure provides protection in harsh environments permitting outdoor monitoring or in areas where dust and particulate matter exists
- Easy to read LCD display provides immediate local alerts allowing corrective action to be taken quicker to eliminate the problem from becoming widespread
- Zero and span controls provides easy calibration checks and shorter installation time to get device running and monitoring

## **APPLICATIONS**

- Dust collection
- Outdoor HVAC
- · Roof-top equipment

## **SPECIFICATIONS**

**Service:** Air and non-combustible, compatible gases.

Wetted Materials: Consult factory. Accuracy: ±0.25% FS @ 77°F (25°C),

display accuracy ±0.5%.

Stability: ±1% FS/yr.
Temperature Limits: -4 to 158°F (-20

to 70°C).

Pressure Limits: See chart.

**Power Requirements:** 10-36 VDC (2-wire), 17-36 VDC, or isolated 21.6-33

VAC (3-wire).

Output Signal: 4-20 mA (2-wire), 0-5 VDC, or 0-10 VDC (3-wire).

Zero and Span Adjustments: Pushbuttons.

**Loop Resistance:** Current output: 0 to 1250  $\Omega$  max; Voltage output: Load resistance 1 k $\Omega$  (min).

Current Consumption: 21 mA max.

Electrical Connections: 4-wire removable European style terminal block for 16 to 26 AWG

**Process Connections:** Barbed, dual size to fit 1/8" and 3/16" (3.12 and 4.76 mm) ID rubber or vinyl tubing.

Enclosure Rating: NEMA 4X (IP66). Mounting Orientation: Any orientation. Weight: Without LCD: 8.9 oz (253 g);

With LCD: 9.5 oz (269 g).

Compliance: CE.

MODEL CHART						
Model	Range	Max. Pressure	Model	Range	Max. Pressure	
616W-3-LCD 616W-4-LCD	0 to 6 in w.c. 0 to 10 in w.c. 0 to 20 in w.c. 0 to 40 in w.c.	4.5 psig 6 psig	616W-6-LCD 616W-20B-LCD 616W-3M-LCD		4.5 psig	
Note: Units with "M" in the model number are metric units.						

OPTIONS				
To order add suffix:	Description			
-NIST	NIST traceable calibration certificate			
Example: 616W-3-LCD-NIST				

Process Tubing Options: See page 453 (Gage Tubing Accessories)