

Type TXF Subminiature Time Delay Fuse - 3.6 x 10mm



www.optifuse.com (619) 593-5050

Agency Standards and Listings:



Time Characteristics:

100%	4h Min.	200mA-10A
200%	60s Max. 1-60s	200mA-800mA 1A-10A


Interrupt Rating:

200mA~ 1.6A 30A at 350 VAC
2A ~ 10A 50A at 350 VAC


Packaging:

1,500 pieces taped and ammo pack

Time Current Curve Graph



Mechanical Dimensions:



Part Number	Amperage	Safety Approval			Rated Voltage (VAC)	I ² T Reference A ² Sec
		UL / CUL	UR / CUR	CSA		
TXF-200mA	200mA		•	•	350V	0.0200
TXF-250MA	250mA		•	•		0.0352
TXF-300mA	300mA		•	•		0.0562
TXF-315mA	315mA		•	•		0.0620
TXF-350mA	350mA		•	•		0.0765
TXF-375mA	375mA		•	•		0.0878
TXF-400mA	400mA		•	•		0.107
TXF-500mA	500mA		•	•		0.219
TXF-600mA	600mA		•	•		0.387
TXF-630mA	630mA		•	•		0.427
TXF-700mA	700mA		•	•		0.642
TXF-750mA	750mA		•	•		0.742
TXF-800mA	800mA		•	•		1.000
TXF-1A	1A		•	•		2.692
TXF-1.2A	1.2A		•	•		3.825
TXF-1.25A	1.25A		•	•		4.111
TXF-1.5A	1.5A		•	•		6.252
TXF-1.6A	1.6A		•	•		7.113
TXF-2A	2A	•		•		13.14
TXF-2.25A	2.25A	•		•		17.46
TXF-2.5A	2.5A	•		•	20.32	
TXF-3A	3A	•		•	31.05	
TXF-3.15A	3.15A	•		•	34.23	
TXF-3.5A	3.5A	•		•	44.25	
TXF-4A	4A	•		•	58.34	
TXF-5A	5A	•		•	90.36	
TXF-6A	6A	•		•	86.25	
TXF-6.3A	6.3A	•		•	95.09	
TXF-7A	7A	•		•	120.8	
TXF-8A	8A	•		•	175.4	
TXF-9A	9A	•		•	228.6	
TXF-10A	10A	•		•	297.8	

Warning:



-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of Fuse device with chemical solvent. Prolonged contact may damage the device performance.