

PNOZ X2.8P C 24VACDC 3n/o 1n/c

787301



Safety relay (standalone), inputs: 1/2-channel wiring with/without detection of shorts across contacts, outputs: 3 N/O, 1 N/C, automatic/manual start, UB 24 V AC/DC, width: 22.5 mm, plug-in spring-loaded terminals, monitoring of E-STOP, safety gates, lightguard.

Technical details

General data	
Approval:	CE, CCC, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	AC/DC
Power consumption AC:	5.5
Power consumption DC:	2.5
Inputs	
Number of inputs:	2
Semiconductor outputs	
Number of semicond. outputs:	0
Relay outputs	
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240
Max. current AC1 safety cont.:	6
Voltage DC1 safety cont.:	24
Max. current DC1 safety cont.:	6
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230

Max. current AC15 safety cont.:	5
Voltage DC13 safety cont.:	24
Safety contacts: AC at UL:	240 V AC G.U. (same polarity)
Safety contacts: pilot duty:	R300
Relay contact material:	AgCuNi
Addit. contact details relay:	+ 0,2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-35 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61000-6-4, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	2
Protection type, mounting:	IP54
Protection type, housing:	P_SCHUTZ_GEHAEU_IP40
Terminal protection type:	IP20
Mechanical data	
Mounting position:	beliebig
Housing material lower section:	PPO UL 94 V1
Housing material front plate:	ABS UL 94 V0
Housing material upper part:	PPO UL 94 V1
Connection terminal:	Federkraftklemme
Terminal style:	steckbar
Height dimension:	101 mm
Width dimension:	22.5 mm
Depth dimension:	121 mm

Net weight:	180 g
Gross weight:	190 g
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449

Optional accessories

374290

PNOZ X Set spring loaded terminals P1+P2

