

PNOZ s7 24VDC 4 n/o 1 n/c

750107



PNOZsigma contact expansion, outputs: 4 N/O, 1 N/C, UB 24 V DC, width: 17.5 mm, plug-in screw terminals, contact block for contact expansion in connection with safety-related control components.

Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	2
Inputs	
Number of inputs:	1
Semiconductor outputs	
Number of semicond. outputs:	0
Relay outputs	
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240
Max. current AC1 safety cont.:	6
Voltage DC1 safety cont.:	24
Max. current DC1 safety cont.:	6
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230
Max. current AC15 safety cont.:	5

Voltage DC13 safety cont.:	24
Safety contacts: AC at UL:	240 V AC G.U. (same polarity)
Relay contact material:	AgCuNi
Addit. contact details relay:	+ 0,2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-10 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61000-6-4, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Protection type, mounting:	IP54
Protection type, housing:	IP40
Terminal protection type:	IP20
Mechanical data	
Mounting position:	beliebig
Housing material lower section:	PC
Housing material front plate:	PC
Housing material upper part:	PC
Connection terminal:	Schraubklemme
Terminal style:	steckbar
Flex. cond. c/s AWG info:	24 - 12 AWG
Height dimension:	98 mm
Width dimension:	17.5 mm
Depth dimension:	120 mm
Net weight:	170 g

Gross weight:	180 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 1317-36-8
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449

Optional accessories



750020

PNOZ s connector (10 pieces)



750003

PNOZ s Setscrew terminals 17,5mm