



1

2

3

4

5



#### TECHNICAL CHARACTERISTICS

##### MATERIAL

INSULATOR: PA 66  
 FLAMMABILITY RATING: UL94-V0  
 COLOR: GREY  
 CONTACT MATERIAL: PHOSPHOR BRONZE - TIN PLATED  
 WIRE GUARD: STAINLESS STRIP STEEL

##### ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 115°C  
 COMPLIANCE: LEAD FREE AND ROHS

##### ELECTRICAL

cULus  
 CURRENT RATING: 16A  
 WORKING VOLTAGE: 300VAC  
 WITHSTANDING VOLTAGE: 2.0KV  
 INSULATION RESISTANCE: 2000 MOhm  
 CONTACT RESISTANCE: 20 mOhm

##### STANDARD

cULus CERTIFIED E315414

##### MECHANICAL

SOLID WIRE: 28-12 AWG / 0.081-3.31 MM<sup>2</sup>  
 STRANDED WIRE: 28-12 AWG / 0.081-3.31 MM<sup>2</sup>

WIRE STRIPE LENGTH: 8-9 MM  
 PITCH: 5.0 MM

PACKAGING  
 BOX

##### DIMENSION

A = 5 x (NB POLES - 1) + 6.5

RoHS Compliant

G				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		
F							
E							
D							
C				APPROVAL: FBr	UNIT: MM	DESCRIPTION: SERIE 369B - 5,00MM SCREWLESS CABLE ENTRY PLUG - WR-TBL	SIZE <b>A4</b>
B	03-DEC-15	RESISTANCE	AK		SCALE:		
A	03-JUN-13	PDF	QL		SHEET: 1/2	WERI PART NO: 691 369 700 0xxB	
REV	DATE	FILE	BY		DRAW: QL		

1

2

3

4

5

## Cautions and Warnings:

This electronic component is designed and developed with the intention for use in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Würth Elektronik must be asked for a written approval.



In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

A

B

C

RoHS Compliant

G				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		
F							
E							
D							
C				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE <b>A4</b>
B					SCALE:		
A	10-SEP-14	PDF	QL		SHEET: 2/2	WERI PART NO: DISCLAIMER	
REV	DATE	FILE	BY		DRAW: QL		

D